



Saudi Arabia – Calibration Services



Smart in sensing

CALIBRATION SERVICES IN THE LABORATORY

MANUFACTURER-INDEPENDENT FOR YOUR DEVICES

With years of experience in measurement and calibration technology, we are your reliable partner for the highest precision and quality. Our extensive team and numerous subsidiaries worldwide use advanced technology to ensure that every calibration meets the highest standards of ISO/IEC 17025. We offer customized solutions that are precisely tailored to your specific requirements.




The blue bars show the beginning and end of the measuring range of WIKA Saudi Arabia. Depending on the measuring range, a calibration certificate accredited and traceable according to ISO/IEC 17025 (GAC, SAAC or other accreditation body) and/or a non-accredited certificate can be created.



Pressure

Pneumatic	-1 bar	...	+100bar*
Hydraulic	0 bar	...	6,000 bar

* up to +200 bar possible with non-accredited certificate



Flow

Mass flow rate	10 l/min	...	18,000 l/min
Flow speed	0 m/s	...	12 m/s



Volume

Volume	1 l	...	1,000 l
--------	-----	-----	---------



Temperature

Measuring	-35 °C	...	+1,100 °C
-----------	--------	-----	-----------



At WIKA



Mobile



At yours



MORE MEASURANDS FROM OUR CALIBRATION OFFER




Electrical

DC Voltage	0.1 V	...	1,000 V
DC Current with Coil	0.1 μ A	...	1,500 A
DC Resistance	0 Ω	...	300 Ω
AC Voltage	0 mV	...	1,000 V
AC Current with Coil	0 μ A	...	1,500 A
Frequency	≥ 0.0001 Hz	...	1 MHz
Power (Single phase)	1 kW	...	30 kW
Capacitance	0 mF	...	100 mF



Dimensions

Linear length	≥ 0 mm	...	1,000 mm
---------------	-------------	-----	----------



Mass

Weighing scales	1 mg	...	600 kg
-----------------	------	-----	--------



At WIKA



Mobile



At yours

OUR CALIBRATION OFFER ON SITE

HIGHLY EQUIPPED CALIBRATION VEHICLES FOR OUTSTANDING SERVICES




Pressure

Hydraulic
Pneumatic



0 bar	...	6 bar
-0.9 psi	...	+25 bar



Flow

Flowrate


130l/min	...	8,300l/min
----------	-----	------------



Electrical

DC Voltage
DC Current
DC Resistance
AC Voltage
AC Current
Frequency
Insulation Resistance
Low Resistance

0 V	...	1,000 V
0 μ A	...	30 A
0 Ω	...	100 M Ω
0 mV	...	1,000 V
0 μ A	...	30 A
≥ 1 Hz	...	1 MHz
100 k Ω	...	100 G Ω
$\geq 0.0001 \Omega$...	200 M Ω



Mass

Weighing scales

1 mg	...	600 kg
------	-----	--------

MORE MEASURANDS FROM OUR ON-SITE CALIBRATION OFFER



Temperature

Measuring

-35°C ... +1,100°C



Level

Measuring

1 feet ... 60 feet



Analytical

pH	0 pH	...	14 pH
Conductivity	0.001 $\mu\text{S}/\text{cm}$...	2,000 mS/cm
H ₂ S Gas	0 ppm	...	25 ppm
Oxygen Detection	0 %	...	30 %
Lowest Explosive Limit	0 % LEL	...	100 % LEL



QUICK

FLEXIBLE

LOCAL!

**MANUFACTURER-INDEPENDENT CALIBRATION
AND REPAIR SERVICES ON-SITE!**



Minimal
downtime



No transport risks,
no shipping costs



Many years of expe-
rience and expertise



At WIKA



Mobile



At yours

CALIBRATION AC- CORDING TO YOUR REQUIREMENTS

**IN THE LABORATORY OR AT YOUR
PREMISES**

Your needs are most important to us. We calibrate your instruments in our laboratory or at your site.

SAUDI ARABIA



We offer interconnected services across the entire product life cycle. More information in our WIKA service brochure.

Your services partner

WIKA Saudi Arabia For Services Co.

Baghlaf Al Sanaiya Aziziya

Al Khobar 34644, Saudi Arabia

Tel. +966 13 808 2229 | services.sa@wika.com

03/2026 Saudi Arabia



Smart in sensing

www.wika.com