

# **Surface Mount Thermometers**

Approx. .535"

**Dual Magnet** Type TI.ST

#### **Thermometers**

Application

Ovens, boilers, process lines, motors, generators

Size

2" (50.8mm) - Type TI.ST

Depth

1/2"

Accuracy

+/- 2% of full scale

Ranges

0/250° F 0/500° F

-20/120° C

-70/70° C

### **Standard Features**

# **Sensing Element**

Bimetal coil

#### Depth

1/2"

# Case

Steel

#### Connection

Dual Magnets - attach to any ferrous metal surface

#### Dials


Polished aluminum with black markings

#### **Pointer**

Aluminum with matte black finish

#### Window

Glass



# Total Performance™

## Ordering Information:

State computer part number (if available) / type number / size / range / connection size and location / options required.

 $Specifications given in this price list represent the state of engineering at the time of printing. \\ Modifications may take place and the specified materials may change without prior notice$ 

WIKA Instrument Corporation

1000 Wiegand Boulevard Lawrenceville, Georgia 30043-5868 Tel: 770-513-8200 Fax: 770-338-5118

http://www.wika.com e-mail: info@wika.com