

# WIKA'S TEN ETM-MRO MODELS FOR 5-DAY DELIVERY

## RTD - RESISTANCE TEMPERATURE DETECTOR MODELS:

**TR10-2:** Industrial RTD Assembly, Head-Nipple-Union-Nipple Design, Various element lengths available, Direct mount into Thermowell, Transmitters available

**TR15-2:** Remote Mounted Industrial RTD Assembly, Various cable and element lengths available, Inserted into Process or Thermowell, Transmitters available

**TR40:** Industrial RTD Sensor, Metal sheathed elements with various lengths, With or without bushings, With insulated lead wires

**TR45:** Hollow Cut-To-Length RTD Sensor, Temporary replacement for failed MGO packed sensor, Minimizes downtime

## TC - THERMOCOUPLE MODELS:

**TC10-2:** Industrial TC Assembly, Head-Nipple-Union-Nipple Design, Various element lengths available, Direct mount into Thermowell, Transmitters available

**TC15-2:** Remote Mounted Industrial TC Assembly, Various cable and element lengths available, Inserted into Process or Thermowell, Transmitters available

**TC40:** Industrial TC Sensor, Metal sheathed elements with various lengths, With or without bushings, With insulated lead wires

**TC45:** Hollow Cut-To-Length TC Sensor, Temporary replacement for failed MGO packed sensor, Minimizes downtime

## TW - THERMOWELL MODELS:

**TW10:** Flanged Thermowell, Solid Machined, 1-2" 150# RF or 300# RF Design, 316 SS or 304 SS Material, Various lengths available, Tapered or Stepped Style

**TW15:** Threaded Thermowell, Solid Machined, 316 SS or 304 SS Material, Various Lengths available, Tapered or Stepped Style

*Note: For faster deliveries, contact your local WIKA Sales Channel listed below.*