High-speed pressure controller Model CPC3050



WIKA data sheet CT 27.56

Applications

- High speed controlling
- End-of-Line production testing
- Pressure calibration
- Automotive
- Oil and Gas

Special features

- Control speed < 4 seconds for 25%FS steps
- Accuracy: 0.020% FS
- Range: -1 ... 210 bar (-15 ... 3,045 psi)
- PACE remote emulation
- Up to two individual transducer ranges



High-speed pressure controller, Model CPC3050

Description

Overview

The CPC3050 High-Speed Pressure Controller is designed with a primary focus on improving throughput in a manufacturing or calibration process. Offering pressure ranges as low as 0 ... 350 mbar (5 psi) up to 210 bar (3,045 psi), the CPC3050 can be the solution for multiple applications. This controller can be configured as a desktop or 19" rack-mount version. Capable of 2 internal reference transducers and a barometric reference, a single CPC3050 can provide a wide range of pressure control and also emulate both absolute or gauge pressure types. The two customizable transducer ranges provide more flexibility for customer needs and pressure range coverage.

Application

The CPC3050 has an accuracy of 0.020%FS and uses a regulator technology that is designed specifically for high speed pressure control; ideal for end of line testing of an automated production and manufacturing line. Along with the high speed, the 0.020% FS accuracy provides adequate calibration requirements for numerous devices designed for the automotive and oil/gas industry.

Functionality

The CPC3050 High-Speed Controller can be operated locally through a simple and intuitive menu that allows users to control and measure pressure. Additionally, it is capable of remote control with software that can drive all the same functions as local operation. Using serial, USB, Ethernet or GPIB, the CPC3050 can be completely setup to function automatically in a process and achieve optimal output of a manufacturing process. With the Mensor legacy command set, along with PACE emulated commands, it can also be a solution for previously defined remote software.

Design

The standard chassis is designed to be a desktop for bench work in a production or engineering environment. For integration into a more automated process, the sleek design fits in a 3U rack mount tray. Along with the same pressure port layout as many other Mensor controllers, the CPC3050 uses a common SAE 7/16-20 threaded pressure ports, which makes it very easy to find the appropriate pressure adapters for most applications.

WIKA data sheet CT $\,\cdot\,$ PN 0019668001C $\,\cdot\,$ 11/2023





Specifications Model CPC3050

Reference pressure transducers model CPR3050				
Pressure Range	Low Pressure (LP) ⁸⁾	High Pressure (HP) ⁷⁾⁸⁾		
Accuracy 1)	0.020% FS ²⁾			
Gauge pressure 3)	0 5 up to 1,500 psi (0 0.35 up to 100 bar)	0 1,500 up to 3,045 psi (0 100 up to 210 bar)		
Absolute pressure 5)	0 15 up to 0 1,515 psi (0 1 up to 0 101 bar)	0 1,515 up to 3,060 psia (0 101 up to 211 bar)		
Bi-directional pressure ³⁾⁴⁾	-2.5 2.5 up to -15 1,500 psi (-0.17 0.17 up to -1 100 bar)	-15 1,500 up to 3,045 psi (-1 100 up to 210 bar)		
Calibration interval	365 days			
Optional barometric reference				
Function	The barometric reference can be used to switch pressure types ⁶⁾ , absolute <=> gauge. With gauge pressure transducers, the measuring range of the transducers must begin with -1 bar (-15 psi) in order to carry out a complete absolute pressure emulation.			
Measuring range	8 17 psi abs. (552 1,172 mbar abs.)			
Accuracy 1)	0.020% of reading			
Pressure units	39 and two freely programmable			

¹⁾ It is defined by the total measurement uncertainty, with the coverage factor (k = 2) and includes the intrinsic performance of the instrument, the measurement uncertainty of the reference instrument, long-term stability, influence of ambient conditions, drift and temperature effects over the compensated range with recommended zero point adjustment every

Base Instrument			
Instrument			
Instrument Version	Standard: desktop case Optional: 19" rack-mounting kit		
Dimensions	See technical drawings		
Weight	approx. 12.7 kg (28 lbs).		
Display			
Screen	7.0" color LCD with resistive touchscreen		
Warm-up time	approx. 15 min.		
Connections			
Pressure connections	5 ports with 7/16"-20 F SAE and 1 port with 10-32 UNF female		
Filter elements	The instrument has a 40-micron filter on all pressure ports.		
Pressure port adapters	Standard: without Optional: 6mm tube, 1/4" tube, 1/4" female NPT, 1/8" female NPT, or 1/8" female BSP		
Barometer port adapters	Standard: barb fitting Optional: 6mm tube, 1/4" tube		
Permissible pressure media	Dry, clean air or nitrogen (ISO 8573-1:2010 class 5.5.4 or better)		
Wetted parts	Aluminum: 6061-T6 / 2024-T4, Stainless Steel: 303 / 304 / 316 / 316L / 13-8 PH, Brass, Nickel, Buna-N, FKM/FPM, Tungsten carbide, Cerazur ceramic, PTFE, PEEK. Glass-filled epoxy, RTV, ceramic, silicone, silicone grease, urethane, 430FR, 300 series CRES.		
Over pressure protection	Safety relief valve for regulator 3,600 psi. ¹⁾		
Permissible pressure			
Supply port	110 - 120% FS or 10 psi (0.69 bar), whichever is greater.		
Measure/Control port	105% FS primary transducer range		

³⁰ days.. 2) FS = Full Span.

³⁾ Ranges from 1,500 to 3,045 psi will be sealed gauge transducers...

¹ The negative portion of a bidirectional range has the same accuracy as the equivalent positive range.
1 The minimum calibrated range of absolute transducers is 600mTorr
2 For pressure type emulation, we recommend a native absolute pressure transducer, since the zero point drift can be eliminated through a zero point adjustment.
3 Minimum primary sensor range must be greater than 1,500/1,515 psi.
3 Secondary range must be within 10:1 ratio of the primary range.

Base Instrument		
Plumbing	≥0.11" (2.8 mm) ID for optimal performance	
Voltage supply		
Power supply	AC 100 120 V, 50/60 Hz; AC 220 240 V, 50/60 Hz	
Power consumption	max 150 VA	
Permissible ambient conditions		
Compensated temperature range	0 to 50 °C (50 to 122 °F)	
Operating temperature range	-20 to 70 °C (-4 to 158 °F)	
Storage temperature range	-20 to 70 °C (-4 to 158 °F)	
Humidity	5 95% r.h. (non -condensing)	
Mounting position	Horizontal	
Control parameters		
Control stability	High Speed: < 0.025% FS primary transducer (Industrial mode: < 0.01% FS primary transducer)	
Control modes	Industrial, High Speed (default), and Custom	
Control time ⁷⁾⁸⁾	3-4 s	
Control range	0 100% FS	
Minimum control pressure 9)	0.025 psi (0.0017 bar) over exhaust pressure or 0.05% FS, whichever is greater.	
Overshoot	< 1% FS in High Speed mode (<0.5% FS in Industrial mode)	
Test volume	0 1000 cc	

 ^{25%} FS pressure steps in High Speed mode in 50cc test volume.
 Time includes default stable delay 0.5s.
 Low point specification is vacuum region for absolute transducers.

Approvals and Certificates				
Logo	Description		Country	
CE	EU Declaration of Conformity European Union EU Importer: WIKA, 63911 Klingenberg, Germany		European Union	
CA	UKCA Declaration of Conformity Importer: WIKA Instruments Ltd, Unit 6 & 7 Goya Business Park, The Moor Road, Sevenoaks Kent, TN15 5GY		Great Britain	
Certificates				
Calibration ¹¹⁾ Standard: A2LA accredited calibration certificate (standard on factory) Optional: DKD/DAkkS calibration certificate		y)		


¹⁰⁾ Warning! This is class A equipment for emissions and is intended for use in industrial environments. In other environments, e.g. residential or commercial installations, it can interfere with other equipment under certain conditions. In such circumstances the operator is expected to take the appropriate measures.11) Calibration in a horizontal position/operating position.

Touchscreen and intuitive operator interface

Shortly after power-up, the standard main screen (see following picture) is displayed. In this menu screen, one can switch between the operating modes using the buttons **MEASURE** (1), **CONTROL** (10) and **VENT** (9). The instrument is a precision pressure controller, whose setup (incl. optional functions) can be easily configured via the touchscreen.

Standard desktop/main screen

ν



- 1 Home application
- (2) General settings
- 3 Control settings
- Display settings
- 5 Programs
- 6 Favorites
- (7) Barometric pressure reading (optional)
- (8) Menu scroll features forward / back
- (9) VENT

Immediately vents the system, including the test assembly connected to the Measure/Control port, to atmosphere.

(10) CONTROL

In control mode the instrument provides a highly accurate pressure at the Measure/Control port of the respective channel at the desired set point.

(11) MEASURE

In measure mode, the pressure present at the Measure/ Control port is measured with high accuracy (if you switch directly from **CONTROL** to **MEASURE** mode, the last controlled pressure in the connected test assembly will be maintained/locked).

- (12) Auxiliary displays either peak, rate or alternate units
- (13) Current pressure unit and type
- (14) Optional bar graph
- (15) Current measuring value
- (16) Tare function
- (17) Entered set point
- (18) Pressure range of the transducers
- (19) Selection of the active transducer or auto-range
- (20) Current application name

Automatic Contamination Prevention System (A-CPS)

Active decontamination

The Automatic CPS can be mounted either in a wall/ rack mount configuration by the keyholes (Figure 8.6.1-A) on either or both side of the accessory or placed on a steady surface as a desktop accessory.


The DUT can be mounted either on top of the accessory for convinient test stand setup or on the back of the accessory for connection with a pressure hose (Figure 8.6.1-B). The not connected port should be sealed by the plug provided to ensure no leakage.

The pressure connection to the Measure/ Control port of the CPC3050 is established by a pressure tube with 7/16" SAE adapters. The Automatic CPS is powered by the CPC3050 using a 3 meter long flexible cable which connects to the Automatic CPS Backplate on the instrument.




A-CPS Specifications	
Operating Conditions	
Maximum operating pressure	3,065 psig (211 bar gauge)
Maximum operating temperature	80 °C (176 F)
Voltage Supply	
Power supply	12 VDC
Power consumption	13 VA
Pressure Connection	
To the M/C port of CPC3050	1 port with 1/4" tube adapted to 7/16"- 20 F SAE
To the DUT	2 ports with Standard: 7/16" - 20 F SAE Option: 6 mm tube fitting, 1/4" tube fitting, 1/4" female NPT fittings, 1/8" female NPT fittings or 1/8" female BSP fittings
Dimensions & Weight	
Dimensions	5.5 in x 10.5 in x 5.5 in (W x H x D)
Weight	3.99 kg (8.8 lbs)

Dimensions mm (in)



Electrical and pressure connections - rear view



- 1 Exhaust port (7/16-20 UNF)
- (2) Barometric reference port (10-32 UNF)
- (3) IEEE-488 interface
- (4) RS-232 interface
- 5 Ethernet port
- 6 Power supply
- (7) USB interface (instrument) for remote communication
- 8 USB interface (host) for service

- 9 Fan
- $\begin{picture}(60,0)\put(0,0){\line(10,0){10}}\put(0,0)$
- 11 Reference port (7/16-20 UNF)
- (12) Measure/Control port (7/16-20 UNF)
- (13) Supply port (7/16-20 UNF)
- (14) Instrument label
- (15) Automatic CPS connector

Accessories

Accessories for CPC3050		Order code
Description		CPX-A-C4
19" rack mount kit with side panels	-R-	
Barometric reference, measuring range 8 17 psi abs, 0.02% rdg.		-6-
Barometric reference, measuring range 552 1172 mbar abs, 0.02%	rdg.	-P-
Barometric reference, measuring range 552 1172 hPa abs, 0.02% rd	-Q-	
Calibration adapter for barometric reference, power supply and softw	are	-5-
Carrying case	-7-	
Adapter set 1/8" female BSP fittings (4x)	-B-	
Adapter set 1/4" tube fittings (4x)	- -	
Adapter set 6mm tube fittings (4x)	-M-	
Adapter set 1/4" female NPT fittings (4x)	-N-	
Adapter set 1/8" female NPT fittings (4x)	-S-	
Kit - block and bleed valve, ≤ 6000 psi	-8-	
Kit - coalescing filter, ≤ 3600 psi	-9-	
Automatic CPS (Contamination Protection System)	-A-	
Replacement filter for automatic CPS		-2-
Ordering information for your enquiry:		
	1. Order code: CPX-A- 2. Option:	∜C4 []

Scope of delivery

- High speed pressure controller model CPC3050 (desktop case)
- Operating instructions
- 1.5 m (5 ft) power cord
- A2LA calibration certificate (standard on factory)

Options

- Pressure adapters
- Interface cable
- Coalescing filter
- Block and bleed valve
- Pressure booster
- DKD/DAkkS calibration certificate
- Barometric calibration sled and software

Ordering Information

CPC3050 / Instrument version / Pressure application / Pressure unit / Type of pressure / Start of measuring range / End of measuring range / Type of certificate / Pressure adapter / Carrying case / Additional order information

© 2023 WIKA Alexander Wiegand SE & Co. KG, all rights reserved.

The specifications given in this document represent the state of engineering at the time of publishing.

We reserve the right to make modifications to the specifications and materials.

In case of a different interpretation of the translated and the English data sheet, the English wording shall prevail.

WIKA data sheet CT · PN 0019668001C · 11/2023

Page 8 of 8



Mensor LP

201 Barnes Drive
San Marcos, TX 78666 • USA
Tel. (+1) 512 3964200-15
Fax (+1) 512 3961820
E-Mail sales@mensor.com
www.mensor.com



Imported to Europe by: WIKA Alexander Wiegand SE & Co. KG

Alexander-Wiegand-Straße 30 63911 Klingenberg • Germany

Tel. +49 9372 132-0 Fax +49 9372 132-406

info@wika.de www.wika.de Imported to UK by: WIKA Instruments Ltd, Unit 6 & 7 Goya Business Park, The Moor Road, Sevenoaks Kent, TN15 5GY

Ε̈́Ν