

Analogue limit switch Model EGS01

WIKA data sheet AC 50.05

Applications

- Measuring and control systems
- Machine building and plant construction
- Manufacturing automation

Special features

- Limit switch for mV/V signals
- 3 relay outputs
- Adjustable control for switching thresholds
- Simple operation and setting
- Case for DIN-rail mounting



Analogue limit switch, model EGS01

Description

The model EGS01 analogue amplifier with relay outputs works as a DC amplifier for strain gauge measuring bridges. Three downstream comparators, each with one adjustment potentiometer, make it possible to set three different switching thresholds, which correspond to a specific load of the connected strain gauge force transducer. Each comparator output controls a relay and a control LED.


When switched off or if the power supply is interrupted, the three relay contacts on the output terminals 3 to 8 are open. When switched-on and below the respective set switching threshold, the output relays are operating and the relay contacts are closed. Parallel to the relay coil, a control LED is switched. It lights up as long as the output contact is closed.

The amplifier is designed for installation in a control cabinet and can be mounted on a mounting rail in a DIN rail housing made of extruded profile.

Specifications

Model EGS01	
Output signal	3 relay outputs
Switching current	max. 3 A
Limiting continuous current	3 A
Switching voltage	DC 250 V / AC 230 V
Switching power	60 W / 120 VA
Filter	adjustable via DIP switch: 10 k Ω , 1 μ F 10 k Ω , 11 μ F 10 k Ω , 21 μ F
Input signal	Resistance thermometry bridges, 4-wire
Measuring range	0 ... 2.1 mV/V DC 5 V, max. 100 mA
Sensor supply	designed for resistance thermometry bridge, 4 x 350 Ω
Measurement accuracy	0.3 %
Setting	continuously adjustable via potentiometer
Rated temperature range	10 ... 40 °C
Service temperature range	0 ... 70 °C
Storage temperature range	-10 ... +70 °C
Supply voltage	DC 24 V -10 %/+15 %, max. 150 mA
Ingress protection	IP20
Dimensions (L x W x H)	107 x 54 x 25 mm

Functions



© 10/2019 WIKA Alexander Wiegand SE & Co. KG, all rights reserved.
The specifications given in this document represent the state of engineering at the time of publishing.
We reserve the right to make modifications to the specifications and materials.