Pressure sensor module Up to 1,000 bar Model MTF-1

WIKA data sheet PE 83.01







Applications

- Sensor integration projects
- Battery-operated applications
- Applications with high pressures of up to 1,000 bar [15,000 psi]
- Implementation of condition monitoring

Special features

- Compact design for limited mounting spaces
- Low energy consumption reduces maintenance effort
- Dry, welded measuring cell from stainless steel for aggressive media
- Additional temperature indication for condition monitoring





Fig. left: Pressure sensor module, spanner width 19 mm Fig. right: Pressure sensor module, spanner width 27 mm

Description

The model MTF-1 pressure sensor module is a simple and flexible option for integrating pressure measurement into a wide variety of applications. The pressure value is digitally processed in the module and output as a standardised digital or analogue signal. Thus, the MTF-1 module delivers precise data for applications with pressures of up to 1,000 bar. Adjustment of the output signal is carried out by WIKA at the factory, meaning time and cost expenditure for calibration during integration is eliminated.

Low energy consumption reduces maintenance effort

The model MTF-1 pressure sensor module is designed for energy-saving operation. The digital I²C signal transmits data extremely efficiently thanks to low basic energy consumption and fast switch-on times.

The energy-efficient sleep mode further reduces energy consumption. This makes the module particularly suitable for battery-operated solutions, ensures long cycles between battery changes and thus reduces maintenance costs.

Dry, welded measuring cell from stainless steel, also for aggressive media

The dry, stainless steel measuring cell is welded to the process connection and can therefore also be used with aggressive media. Even after long periods of use with many load cycles, the dry measuring cell of the model MTF-1 only exhibits a low signal drift – and ensures a permanently reliable data basis.

Additional temperature indication for condition monitoring

In order to evaluate the condition of the sensor, in many applications a temperature indication is helpful. Thanks to the digital I²C protocol, parallel to the pressure signal, the model MTF-1 provides a guideline value for the temperature in the sensor module, which can be used for condition monitoring of the instrument. With condition-based and preventive maintenance made possible by this, the service life can be significantly extended and repairs can be planned ahead.

Explosion protection

Optionally, the model MTF-1 is available with ATEX and IECEx approval.

WIKA data sheet PE 83.01 · 03/2022

Page 1 of 10



Specifications

The model MTF-1 features a pressure output as standard. In versions with the I²C output signal the pressure sensor module has an additional temperature output. The following specifications refer to the pressure outlet. For details on the temperature output, see table "Optional temperature output".


Optionally the model MTF-1 is available with an improved non-linearity. Depending on the selected non-linearity the following values result:

Accuracy specifications	Non-linearity ≤ ±0.25 % of span	Non-linearity ≤ ±0.125 % of span			
Non-linearity per BFSL per IEC 62828-1	$\leq \pm 0.25 \%$ of span $\leq \pm 0.125 \%$ of span				
Accuracy	→ See "Max. measuring deviation per IEC 62828-1"				
Max. measuring deviation per IEC 62828-1	≤ ±0.5 % of span	$\leq \pm 0.25$ % of span ¹⁾			

¹⁾ With I^2C only possible with oversampling ≥ 4

Further details on: Accuracy specifications				
Signal noise	≤ ±0.2 % of span			
Non-repeatability per IEC 62828-1	■ \leq 0.1 % of span for analogue signals and I ² C with oversampling \geq 4 ■ \leq 0.15 % of span for I ² C with oversampling $<$ 4			
Influence of supply voltage	Max. ±0.1 %/10 V (for signal 1 10 V)			
Max. temperature error	→ See below			
Long-term drift per IEC 62828-1	≤ ±0.1 % of span			
Reference conditions	Per IEC 62828-1			

Temperature error



For pressure ranges < 10 bar/150 psi, a higher temperature error at below -20 °C [-4 °F] and above 60 °C [140 °F] must be taken into account.

Measuring ranges, gauge pressure

bar	
0 10	0 160
0 16	0 250
0 25	0 400
0 40	0 600
0 60	0 1,000
0 100	

psi	
0 100	0 1,000
0 150	0 1,500
0 160	0 2,000
0 200	0 3,000
0 250	0 4,000
0 300	0 5,000
0 400	0 6,000
0 500	0 7,500
0 600	0 10,000
0 750	0 15,000

Measuring ranges, vacuum and +/- measuring range

bar	
-1 +9	-1 +24
-1 +15	

psi	
-14.5 +160	-14.5 +300
-14.5 +200	

Other measuring ranges on request.

Further details on: Measuring range			
Overpressure limit 1)			
Measuring ranges ≤ 600 bar/7,500 psi	2 times		
Measuring ranges > 600 bar/7,500 psi	1.43 times		
Vacuum resistance	Yes		

¹⁾ The overpressure limit is based on the sensor element used. Depending on the selected process connection and sealing, restrictions in overpressure limit can result. With increased overpressure limit there are deviations in temperature error and long-term stability.

Process connection						
Standard	Thread size	Max. measuring range	Overpressure limit	Sealing		
EN 837	G 1/8 B	400 bar [5,800 psi]	572 bar [8,290 psi]	Copper		
	G 1/4 B	1,000 bar [15,000 psi]	1,480 bar [21,400 psi]	CopperStainless steel		
	G ½ B			CopperStainless steel		
DIN EN ISO 1179-2 (formerly DIN 3852-E)	G 1/8 A	250 bar [3,000 psi]	358 bar [5,190 psi]	FPM/FKM		
	G 1/4 A	600 bar [8,700 psi]	858 bar [12,400 psi]	■ NBR ■ FPM/FKM		
	G ½ A	600 bar [8,700 psi]	858 bar [12,400 psi]	■ NBR ■ FPM/FKM		
DIN EN ISO 9974-2 (formerly DIN 3852-E)	M10 x 1.0	250 bar [3,000 psi]	358 bar [5,190 psi]	FPM/FKM		
ANSI/ASME B1.20.1	1/4 NPT	1,000 bar [15,000 psi]	1,480 bar [21,400 psi]	-		

Further details on: Process connection					
Max. measuring range	→ See above				
Overpressure limit	→ See above				
Sealing	→ See above				
Pressure port diameter	3.5 mm (standard for all process connections)				
Possible restrictions	Depending on the choice of sealing on the process connection, there may be restrictions in the permissible temperature range.				
NBR	-20 +100 °C [-4 +212 °F]				
FPM/FKM	-20 +125 °C [-4 +257 °F]				

Other process connections, sealings and pressure port diameters on request.

Output signal					
Signal type					
Analogue	DC 1 10 V				
	DC 0.5 4.5 V ratiometric				
Digital	I ² C				
Load in Ω					
DC 1 10 V	≥ 10 k				
DC 0.5 4.5 V ratiometric	≥ 4.5 k				
Signal clamping (optional for an	alogue signals)				
DC 1 10 V	Zero point	DC 0	0.5 V		
	Full scale	DC 1	1.5 V		
DC 0.5 4.5 V ratiometric	Zero point	DC 0	0.25 V		
	Full scale	DC 4	7.75 V		
Communication, digital signal	The MTF-1 is designed as a slave in the I²C bus and sends a pressure value to the master when it requests this. If no request occurs, the MTF-1 switches to the power-saving "sleep mode". → For a detailed description, see "I²C protocol for models MPR-1 and MTF-1" at www.wika.com.				
Communication protocol	I ² C				
Voltage supply					
Supply voltage	DC 1 10 V		DC 12 30 V		
	DC 0.5 4.5 V ratiometric		DC 5 V ±10 %		
	I ² C		1.8 3.6 V		
Current supply	DC 1 10 V		≤ 3.5 mA		
	DC 0.5 4.5 V ratiometric		≤ 3.5 mA		
	I ² C		≤ 2 mA with measurement≤ 1 µA in sleep mode		
Dynamic behaviour					
Settling time per IEC 62828-1	Analogue signals		1 ms		
	Digital signals		 6 ms with oversampling = 1 (includes the switch-on time) 24 ms with oversampling = 4 (includes the switch-on time) 		
Switch-on time	Analogue signals		20 ms		
	Digital signals		2.5 ms		
Start-up drift	200 ms (only for analogue signals, not valid for I ² C)				
Response time I ² C	 3 ms with a pulse frequency of ≥ 400 kHz (oversampling = 1) 12 ms with a pulse frequency of ≥ 400 kHz (oversampling = 4) 				

Other output signals on request.

Electrical connection				
Connection type	JST female connector, 6-pin			
Pin assignment	→ See below			
Ingress protection (IP code) per IEC 60529				
Spanner width 19 mm	IP-3x			
Spanner width 27 mm	IP-1x			
Short-circuit resistance				
Analogue signals	S+ vs. U-			
Digital signals	U+ and U- vs. SDA, SCL, RES			
Reverse polarity protection	U+ vs. U- (only for analogue signals)			
Insulation voltage				
Standard version	DC 500 V			
Version with explosion protection	DC 850 V			

Other electrical connections on request.

Pin assignment

JST female connector, 6-pin (model BM06B-SRSS-TB)				
		3-wire	I ² C	
	U+	1	1	
666666	U-/GND	4	4	
	S+	2	-	
	SDA	-	5	
	SCL	-	6	
	EOC	-	2	
	Reset	-	3	

Legend

U+ Positive power supply terminal U-/GND Negative power supply terminal/ground

S+ Analogue output
EOC End of conversion
SCL Serial clock
SDA Serial data

Other pin assignments on request.

Material				
Material (wetted)				
Process connection and sensor	Stainless steel 316L, PH grade steel			
Sealing	→ See "Process connection"			
Material (in contact with the environment)				
Case	Stainless steel 316L			
Potting	Silopren®			
Cover	PBT GF30			

Operating conditions				
Medium temperature limit 1)	-40 +125 °C [-40 +257 °F]			
Ambient temperature limit 1)	-40 +125 °C [-40 +257 °F]			
Storage temperature limit	-40 +70 °C [-4 +158 °F]			
Vibration resistance per IEC 60068-2-6	EC 60068-2-6 20 g, 10 2,000 Hz			
Shock resistance per IEC 60068-2-27	600 g, 1 ms			
Free fall per IEC 60068-2-31				
Individual packaging	1 m [3.3 ft]			
Multiple packaging	0.5 m [1.6 ft]			
Ingress protection (IP code) per IEC 60529	→ See "Electrical connection"			
Service life	 100 million load cycles 10 million load cycles for measuring ranges > 600 bar/7,500 psi 			

¹⁾ Depending on the choice of sealing on the process connection and the electrical connection, there may be restrictions in the medium and ambient temperature ranges (¬ for restrictions, see "Process connection" and "Electrical connection").

Options for specific media					
Oil- and grease-free					
Residual hydrocarbon	< 1,000 mg/m ²				
Oxygen, oil- and grease-free	Oxygen, oil- and grease-free				
Residual hydrocarbon	< 200 mg/m ²				
Packaging	Protection cap on the process connection, sealed in a vacuum bag				
Max. permissible temperature range	-20 +60 °C [-4 +140 °F]				
Max. measuring range	400 bar [5,800 psi]				
Sealing	Stainless steel				

Optional temperature output					
Output signal	Only available for output signal I ² C				
Measuring range	-20 +100 °C [-4 +212 °F]				
Accuracy	→ See "Max. measuring deviation"				
Max. measuring deviation					
For measuring range -20 +60 °C [-4 +140 °F]	±3.5 K				
For measuring range > 60 80 °C [140 176 °F]	±4.75 K				
For measuring range > 80 100 °C [176 212 °F]	±6 K				

Packaging and instrument labelling			
Packaging	Individual packaging		
	Multiple packaging	■ Up to 45 pieces possible (spanner width 19 mm) ■ Up to 25 pieces possible (spanner width 27 mm)	
Instrument labelling	WIKA product label, laseredCustomer-specific product label on request		

Optional approvals

Logo	Description		Region
⟨£x⟩	Attestation of conformity	European Union	
(2)	ATEX directive Hazardous areas - Ex i Zone 1 mounting to zone 0 gas Zone 0 gas Zone 21 mounting to zone 20 dust Zone 20 dust	II 1/2G Ex ia IIC Ga/Gb II 1G Ex ia IIC Ga II 1/2D Ex ia IIIC Da/Db II 1D Ex ia IIIC Da	
IEC IECEX	IECEx Hazardous areas - Ex i Zone 1 mounting to zone 0 gas Zone 0 gas Zone 21 mounting to zone 20 dust Zone 20 dust	Ex ia IIC Ga/Gb Ex ia IIC Ga Ex ia IIIC Da/Db Ex ia IIIC Da	International

Manufacturer's information

Logo	Description
-	China RoHS directive
-	Yield strength EN 61010-1 section 11.7 and annex G

Test report

Test report	
Non-linearity 0.25 %	3 measuring points
Non-linearity 0.125 %	3 measuring points

Certificates (option)

Certificates	
Certificates	2.2 test report per EN 10204 (e.g. state-of-the-art manufacturing, material proof, indication accuracy)


[→] For approvals and certificates, see website


Safety-related characteristic values (Ex)				
Max. connection values 1)				
Voltage U _i	DC 10 V			
Current I _i	400 mA for gas applications			
	250 mA for dust applications			
Power P _i	■ 150 mW ■ 250 mW ■ 500 mW			
Effective internal capacitance Ci	500 nF			
Effective internal inductance Li	Negligible			

Safety-related characteristic values (Ex)					
Ambient temperature ranges (ambient temperature = medium temperature)					
Min. temperature for gas applications	-40 °C [-40 °F]				
Max. temperatures for gas applications	150 mW	T4	119 °C [246 °F]		
		T5	84 °C [183 °F]		
		T6	69 °C [156 °F]		
	250 mW	T4	115 °C [239 °F]		
		T5	80 °C [176 °F]		
		T6	65 °C [149 °F]		
	500 mW	T4	100 °C [212 °F]		
		T5	65 °C [149 °F]		
		T6	50 °C [122 °F]		
Min. temperature for dust applications	-40 °C [-40 °F]				
Max. temperatures for dust applications	500 mW	T135	100 °C [212 °F]		

¹⁾ These parameters must be complied with via the electronics of the pressure measuring instrument.

Dimensions in mm [in]







Process connections


Spanner width 19 mm




G	L1
G 1/8 A DIN EN ISO 1179-2	9.5 [0.37]
G 1/4 A DIN EN ISO 1179-2	14 [0.55]
M10 x 1.0 DIN EN ISO 9974-2	14 [0.55]










Spanner width 27 mm



G	L1
G 1/4 A	14 [0.55]
G ½ A	17 [0.67]







Accessories

Model	Description		Order number
	G 1/8 B EN 837	Copper	11251051
		Stainless steel	14124338
	G 1/4 B EN 837	Copper	11250810
		Stainless steel	11250844
	G 1/8 A EN 837	FPM/FKM	14170413
	M10 DIN EN ISO 9974-2	FPM/FKM	14170413
	G ¼ A DIN EN ISO 1179-2	NBR	1537857
		FPM/FKM	1576534
	G ½ B DIN EN ISO 1179-2	Copper	11250861
		Stainless steel	11251042
	G ½ A DIN EN ISO 1179-2	NBR	1039067
		FPM/FKM	1039075

Ordering information

Model / Design / Measuring range / Output signal / Non-linearity / Process connection / Sealing / Electrical connection / Certificates / Accessories

© 09/2021 WIKA Alexander Wiegand SE & Co. KG, all rights reserved.

The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials.

WIKA data sheet PE 83.01 · 03/2022

Page 10 of 10



Fax +49 9372 132-406 info@wika.de www.wika.de