

Differential Pressure Transmitter

with Diaphragm, Pressure rating PN 40/100/250 bar

Standard • Model 891.34.1884

TRONIC LINE

- Pressure ranges from 0 ... 40 mbar to 0 ... 25 bar
- Wetted parts and case of stainless steel and NiCrCo alloy (Duratherm) and FPM/FKM
- Pressure connections 2 x G ½ female
- For gaseous, liquid and aggressive media, and in aggressive environments
- Differential pressure measurement at points with a high differential pressure overload and/or a high working pressure
- Max. working pressure (static pressure) alternatively 40, 100 or 250 bar
- High overload value either side alternatively 40, 100 or 250 bar
- Transmitter with Hall sensor and amplifier
- Industrial standard signals 4 ... 20 mA or 0 ... 20 mA
- Electrical connection via cable box
- Ingress protection IP 65



General features

The principle feature of these differential pressure gauges with mounted transmitter is their high overload value in conjunction with high working pressures.

The differential pressure transmitter consists mainly of a mechanical measuring system with elastic pressure element of Model 732.14, magnetic-field-dependent sensor (Hall sensor) with amplifier and case with the connecting parts for the electronics.

A permanent magnet rigidly coupled to the pressure element influences the flow field of a sensor. The resulting differential voltage is amplified to a standard current signal.

Standard output signals of 4 \dots 20 mA (2 wire system) or 0 \dots 20 mA (3 wire system) can be provided from a non-stabilized DC supply of 10 \dots 30 V.

Upon request, the transmitters may also be supplied in intrinsically safe ex-approved design with the output signal 4 ... 20 mA.

For recalibration, zero and span can be adjusted by means of easily accessible potentiometers.

The use of high-quality stainless steel material is intended for applications within the chemical industry for gaseous, liquid and aggressive media. Typical applications are, for example, the monitoring of pumps, filters and compressors.

Wetted parts made of special materials can be supplied where increased resistance to corrosion is required.

Electrical connection is made by means of a cable box with screwed cable gland M20 x 1.5.

Supplementary data sheets

 Differential pressure transmitter Pressure rating PN 2.5/25/40 bar (see data sheet PE 81.70)

Model 89X.34.2166

Model 89X.34.1998

 Pressure transmitter high overpressure safety (see data sheet PE 81.74)

Model 89X.34.2082

 Absolute pressure transmitter (see data sheet PE 81.76)

 Transmitter to combine with pressure gauges Model 89X.34 (see data sheet AE 08.02)

Gauge head geometry [□ mm]	Pressure ranges	Working pressure (static pressure) maximum [bar] alternatively	Overpressure safe (either side) maximum [bar]
140	0 40 mbar to 0 60 mbar	40, 100 or 250	up to respective working pressure max. (static pressure)
80	0 0.1 bar to 0 25 bar		

Process connections: 2 x G $\frac{1}{2}$ female (optional: 2 x $\frac{1}{2}$ NPT female, 2 x $\frac{1}{2}$ NPT male with adaptors 2 x G $\frac{1}{2}$ B male with adaptors, pressure connection per DIN 19 213)

Technical data		Model 891.34.1884 and Model 892.34.1884 (@-version)		
Power supply $U_{\rm B}$				
for non - 🕲 -class Models	DCV	$10 < U_{\rm B} \le 30$		
for 🚱 -class Models		see under section 🔂 -class protection		
Supply voltage effect	% of span/10 V	≤ 0.1		
Permissible residual ripple	% ss	≤10		
Output signal		for non & -class version, Model 891.34.1884:		
and permissible max. load R_A		4 20 mA, 2-wire system $R_A \le (U_B - 10 \text{ V}) / 0.02 \text{ A}$ with R_A in Ohm and U_B in Volt		
		020 mA, 3-wire system $R_A \le (U_B - 10 \text{ V}) / 0.02 \text{ A}$ with R_A in Ohm and U_B in Volt		
		$\{0 \dots 10 \text{ V}, 3\text{-wire system } R_A \leq (U_B - 10 \text{ V}) / 0.02 \text{ A} \text{ with } R_A \text{ in Ohm and } U_B \text{ in Volt}\}$		
		for Go -class version, Model 892.34.1884:		
		420 mA, 2-wire system $R_A \le (U_B - 12.5 \text{ V}) / 0.02 \text{ A}$ with R_A in Ohm and U_B in Volt		
Effect of load	% of span	≤ 0.1		
Response time	S	approx. 1 (optional approx. 0.05)		
Output signal adjustment				
Zero point, electrical	% of span	± 15		
Span, electrical	% of span	±30		
Linearity	% of span	± 1.2 (0.8) (limit point calibration)		
Hysteresis	% of span	≤ 0.8 {0.5}		
Permissible				
Medium temperature 1)	°C	-25+100		
Ambient temperature 1)	°C	-20+60		
Compensated temperat. range	°C	-25+60		
Temperature coefficient in				
compensated temperat. range				
average $T_{ m C}$ on zero point	% of span/10 K	≤ 0.3		
average $T_{\rm C}$ on span	% of span/10 K	≤ 0.3		
-class protection		according to EC-Type Examination Certificate DMT 01 ATEX E 021 for Model 892.34		
Output signal		420 mA, 2-wire		
Ex certification				
Conformity specifications				
Power supply	DC V	12.5 28		
Short circuit rating	mA	100		
Rating	mW	1000		
Internal capacitance	nF	<i>C</i> _i ≤ 24		
Internal inductance	mH	$L_i \leq 0,2$		
Medium temperature	°C	-20+60		
Ambient temperature	°C	-20+60		
C€ -Conformity		Interference emission and immunity per EN 61 326		
Wiring		Terminal box (screw terminals up to 2.5 mm²)		
Wiring protection		Protected against reserve polarity and overvoltage		
Ingress protection		ID OF		
per EN 60 529 / IEC 529		IP 65		
Weight	len.	200 / 200 /		
non 🕝 -class Models	kg	approx. 12.5 (gauge head ☐ 140 mm) or approx. 3.6 (gauge head ☐ 80 mm), respect.		
-class Models	kg	approx. 12.6 (gauge head ☐ 140 mm) or approx. 3.9 (gauge head ☐ 80 mm), respect.		
Dimensions	mm	see drawings		
Items in curved {} brackets are optional extras for additional price.				

¹⁾ for maximum values of Ex-class versions: see 🚳 -class protection

Power supply devices for Differential Pressure Transmitter Model 891.34.1884 under non- @ -operation

For non- @-operation the following power supply devices are available for DC-supply of transmitter Model 891.34.1884:

Model A-VA-1 (old Model 903.30.400) - Power supply, line voltage AC 230 V, output voltage DC 24 V, 70 mA max. Model KFA6-STR-1.24.500 - Power supply, line voltage AC 90 ... 253 V, 48 ... 63 Hz, output voltage DC 24 V, 500 mA max.

-Line transformer for Differential Pressure Transmitter Model 892.34.1884 under & -operation


For log -operation the following log -line transformers are available for galvanical separation and transfer of power supply for transmitter Model 892.34.1884:

Model KFD2-STC4-Ex1 -

- Inne transformer, line voltage: DC 20 ... 32 V, output voltage: DC 25.4 V maximum, 88.2 mA max.

The line transformer is usable with power supply or electronic indicating instrument with integrated power supply for transmitter. When calculating the permissible max. load $R_{\rm A}$ a voltage drop of 7.7 V at the line transformer has to be considered.


Dimensions in mm



- ① Gauge head □ 80 mm (pressure ranges ≥ 100 mbar)
- ② Gauge head ☐ 140 mm (pressure ranges < 100 mbar)

Position of the potentiometers in the electronics case


The potentiometers are accessible after unscrewing the screw plugs in the top of the casing.




Connection details

The terminals 1 and 5 are bridged internally in the terminal box providing two terminals for the 0 V / S- connection.

4...20 mA 2-wire system




0 ... 20 mA 3-wire system



Optional version

Mounting device for surface or pipe mounting



1330 926.01

Ordering information

Model / Pressure range / Working pressure max. (static pressure rating) ... bar / Size and location of connection / Output signal / Optional extras required

Specifications and dimensions given in this leaflet represent the state of engineering at the time of printing. Modifications may take place and materials specified may be replaced by others without prior notice.

