Diaphragm-Type Sanitary Gauge Type M932.25 - Dry Case Type M933.25 - Liquid Filled Case

WIKA Datasheet M93X.25

Applications

- Pharmaceutical Industry
- Biotechnology
- Food & Beverage

Standard Features

Design

External, flush diaphragm with Tri-Clamp® connection, requires hydraulic fluid to transmit pressure to instrument. Unit is autoclaveable when dry case and polysulfone window are specified.

Process Connection

3/4" & 1" Tri-Clamp® per ASME BPE, Type A

Pressure Ranges

1,200 psi maximum, limited by installed clamp rating

Operating Temperature

Media: +10°C to 100°C(standard)

(>100°C available - consult factory) Stainless steel case with vent plug

Ambient: +10°C to 60°C

Gauge Size

21/2", lower mount

Dial

White aluminum with black lettering

Accuracy (Ref. 73°F)

±2/1/2% full span (ASME B40.100, Grade A)

Available Options (Connections, materials, etc.): See Selection Guide on page 3

Temperature Error (Ref. 73°F)

±1.3 psi / 18°F (10°C)





Fig. left M93X.25 Sanitary Gauge Fig. right Clean Steam Assembly

Wetted Parts

316L SS, electro-polished RA \leq 15 μ in (except weld seam)

System Fill (FDA Approved)

Glycerine, 99.7%: Non-vacuum applications Mineral Oil, Neobee M20, 350cST Food Grade Silicon Oil

Material Identification and Heat Numbers

Engraved in seal body or gauge case

Case Material

Polished stainless steel case with vent plug and stainless steel polished ring

Window

Standard polycarbonate
Polysulfone available (with dry case & weep holes)

Serial Number

Engraved on back of case

Pointer

Black aluminum

WIKA Datasheet M93X.25 10/2017






Documentation

Calibration Conformance Report supplied with each assembly (not a direct substitute for NIST certificate). Material Conformance documents supplied with each assembly (not a substitute for 3.1 material certificate)

Available Options

See selection guide (over)
Glyerine case fill
External zero adjust
Autoclaveable (dry case only, weepholes)
Clean steam assembly with integral cooling element
EPDM gasket (consult factory)

To determine the effects of temperature and response time in a specific application, contact the factory for an *Application Questionnaire*. The information provided will allow WIKA Technical Support to accurately model your application parameters using state-of-the-art computer simulation techniques.



			_				
M93X.25 Selection Guide							
Field	Code	Description - 21/2" Gauge with Diaphragm		Field	Code		
no.	Code	Seal - all SST Internals		no.			
		Pressure Range					
	C030	-30 inHg 30 psi Compound range			ES		
	C060	-30 inHg 60 psi Compound range					
	C100	-30 inHg 100 psi Compound Range			HC		
	C160	-30 inHg 160 psi Compound Range		4	XX		
	P030	30 psi Gauge pressure range					
	P060	60 psi Gauge pressure range			07		
	P100	100 psi Gauge pressure range			07		
	P160	160 psi Gauge pressure range			59		
	P200	200 psi Gauge pressure range			- 55		
	P300	300 psi Gauge pressure range			00		
	P400	400 psi Gauge pressure range			92		
	P600	600 psi Gauge pressure range					
1	XXXX	Other - consult factory			93		
		Pressure Units					
	PX	PSI - Single scale		5	XX		
	PC	PSI outside / KG/CM² inside in red					
	PK	PSI outside / KPA inside in red			LPC		
	PB	PSI outside / BAR inside in red		6	LPS		
2	SP	Special scale					
		Process Connection			FGL		
	75	3/4" Tri-Clamp® connector					
	10	1" Tri-Clamp® connector			XMT		
3	XX	Other - consult factory			WSS		
				I	VV 00		

Code	Description - 21/2" Gauge with Diaphragm									
5006	Seal - all SST Internals									
	Wetted Parts Material									
ES	Electropolished 316L SS (1.4435) Ra ≤ 15 μin (except for weld seam)									
HC	Hastelloy C276 (2.4819)									
XX	Other - consult factory									
	System Fill									
07 KN7 - Glycerine 99.7% USP (1000 csi - FDA 21 CFR 182.1320 (see no										
59	KN59 - Neobee M20 - FDA 21 CFR 172.856, 174.5									
92	KN92 - Mineral Oil LubePharm (23 cst) - FDA 21 CFR 172.878, 178.3620 (a); USP, EP									
93	KN93 - Silicone Oil DC200 (350 cst food grade) - FDA 21 CFR 173.340									
XX	Other - consult factory									
	Window Material									
LPC	Polycarbonate									
LPS	Polysulfone									
Options (see note 2)										
FGL Glycerine case fill - change model # to M933.25										
XMT	Material Certificate 3.1 EN10204 (metal only) (see note 3)									
WSS	Instrument tag, Stainless steel									
DZA	External Zero Adjust									
CE1	Integral cooling element (Tmax 300°F, clean steam assembly)									
XAC	Autoclave design, case with 2 weep holes (see note 4)									
VALU	NIST - Certificate of Calibration									
	HC XX 07 59 92 93 XX LPC LPS FGL XMT WSS DZA CE1									

Notes

- 1) Glycerine (07) is not available for vacuum & compound pressure measurement ranges or autoclave design. Consult factory for exceptions.
- 2) List options in alphabetical order at the end of the configuration code.

1

- 3) All product under this model series is provided with calibration protocol, electropolished finish, and material based information report as standard.
- 4) Autoclave design requires Polysulfone window (WPS) and dry gauge case (932.25).

2

Order Code:

M932.25 .	. LM	•	•	•	•	
*Additional order details						

4

5

6

7

3

NOTE: If gauge is to be used in Autoclave, order a dry case and polysulfone window.

Specifications given in this price list represent the state of engineering at the time of printing. Modifications may take place and the specified materials may change without prior notice.

WIKA Datasheet M93X.25 10/2017

Page 3 of 3

Ordering information

Pressure gauge model / Nominal size / Scale range / Size of connection / Optional extras required. Specifications and dimensions given in this leaflet represent the state of engineering at the time of printing. Modifications may take place and materials specified may be replaced by others without prior notice.



WIKA Instrument, LP

1000 Wiegand Boulevard Lawrenceville, GA 30043-5868 Tel: 888-WIKA-USA • 770-513-8200

Fax: 770-338-5118 E-Mail: info@wika.com www.wika.com