

Diaphragm-Type Diaphragm Seals

Mini Diaphragm Seal Type L990.TB

OBSOLETE

Diaphragm Seals

Application

Process industry diaphragm seal to combine with Bourdon tube pressure gauges. Intended for corrosive, contaminated, hot or viscous pressure media.

Design

Upper and lower housing welded with integral diaphragm It requires hydraulic fluid to transmit pressure to instrument

Process Connection

1/4" or 1/2" NPT-female, other see options

Instrument Connection


1/4" or 1/2" NPT-female


Suitable Pressure Ranges (MWP 2500PSI @250°F)

2 ½" gauge: 15 PSI to 2500 PSI 4 or 4 ½" gauge: 15 PSI to 2500 PSI

Available Options

See Selection Guide (over)





To determine the effects of temperature and response time in a specific application, contact the factory for an *Application Questionnaire*. The information provided will allow WIKA Technical Support to accurately model your application parameters using state-of-the-art computer simulation techniques.



G1:	INSTRUMENT CONNECTION

G2: PROCESS CONNECTION
DM: EFFECTIVE DIAPHRAGM DIAMETER
ALL DIMENSIONS IN INCHES UNLESS OTHERWISE NOTED

G1	G2	A	В	С	DM	Ε	F	WEIGHT
								lbs.
1/4"NPT OR 1/2"NPT	1/4"NPT OR 1/2"NPT	2.50 ACROSS FLATS	1.56	2.38	2.1	1.94	1.04	1.4
1/4"NPT OR 1/2"NPT	3/4"NPT OR 1"NPT	2.50 ACROSS FLATS	1.56	2.38	2.1	2.24	1.34	1.5

DWG.#2089077-5

Selection Guide – 990.TB

990.TB,1/4X1/4F,SS,SS-0,SS

Diaphragm Material SS = 316 stainless steel

MO = Monel® 400 (See note 2) HC = Hastelloy® C-276

HB = Hastelloy® B-2 CA = Carpenter® 20 (See note 2)

Flushing Connection

0 = None

1 = 1/8" NPT female

2 = 1/4" NPT female (see note 3)

Lower Housing Material

SS = 316 stainless steel

MO = Monel® 400 (See note 2)

HB = Hastelloy® B-2

HC = Hastelloy® C-276

CA = Carpenter® 20 (See note 2)

Upper Housing Material

SS = 316 stainless steel

MO = Monel® 400 (See note 2)

HC = Hastelloy® C-276 CA = Carpenter® 20 (See note 2)

Process Connection

1/4F = 1/4" NPT female

1/2F = 1/2" NPT female

3/4F = 3/4" NPT female 1.0F = 1" NPT female

1/4M = 1/4" NPT male

1/2M = 1/2" NPT male

3/4M = 3/4" NPT male

1.0M = 1" NPT male

Instrument Connection

1/4 = 1/4" NPT female

1/2 = 1/2" NPT female

CPL= Capillary connection (to weld capillary directly to seal)

Diaphragm Seal Design

990.TB = Large Diaphragm Design, d_w=2.1" (See note 1) MWP = 2500 PSI

Items in bold are available from stock (subject to prior sales). For optional items, consult factory for current lead-time.

Options not listed may be available, please consult factory. Fill Fluid & Mounting options: Please reference data sheet ACS 99.MO.

THE MEASURE OF Total Performance™

Ordering Information:

Notes

PSI to 0-2500 PSI.

1. Suitable pressure ranges 0-15

2. Upper housing, lower housing

and diaphragm must all be Monel®. 3. Available from stock with stainless steel lower housing only.

State computer part number (if available) / type number / size / range / connection size and location / options required.

Specifications given in this price list represent the state of engineering at the time of printing. Modifications may take place and the specified materials may change without prior notice



WIKA Instrument Corporation

1000 Wiegand Boulevard Lawrenceville, Georgia 30043-5868 Tel: 770-513-8200 Fax: 770-338-5118

http://www.wika.com e-mail:diaphragmseal@wika.com