# Bourdon tube pressure gauge, copper alloy or stainless steel Edgewise panel design Models 214.11, 234.11

WIKA data sheet PM 02.07










for further approvals see page 3

## **Applications**

- For gaseous and liquid media that are not highly viscous or crystallising and will not attack copper alloy parts
- Model 214.11: Measuring system copper alloy Model 234.11: Measuring system stainless steel, also for aggressive media



- Built-in case per DIN 43700
- Nominal sizes NS 96 x 96 and NS 72 x 72 available
- Ingress protection IP42



Bourdon tube pressure gauge model 214.11, NS 96 x 96, edgewise panel design

# **Description**

The models 214.11 and 234.11 have been specifically designed for panel mounting and therefore feature a back mount process connection. With their outer dimensions of  $96 \times 96$  mm and  $72 \times 72$  mm in accordance with DIN 43700, the instruments can be installed in corresponding control cabinets and operator panels without any need for adaptation.

Panel mounting is simply carried out using two clamping brackets directly screwed to the case.

The instruments are based on the proven Bourdon tube measuring system. On pressurisation, the deflection of the Bourdon tube, proportional to the incident pressure, is transmitted to the movement via a link and indicated.

The wetted parts of model 214.11 are made of a copper alloy, those of model 234.11 are made of stainless steel.



## **Specifications**

#### Design

DIN 43700

#### Nominal size in mm

96 x 96, 72 x 72

#### **Accuracy class**

NS 96 x 96: Class 1.0

NS 72 x 72, 96 x 96: Class 1.6

#### Scale ranges

NS 96 x 96: 0 ... 0.6 to 0 ... 1,000 bar NS 72 x 72: 0 ... 0.6 to 0 ... 400 bar

or all other equivalent vacuum or combined pressure and

vacuum ranges

### Permissible temperature

Ambient: -20 ... +60 °C

Medium: +60 °C maximum (soft soldered)

+100 °C maximum (brazed)

#### Pressure limitation

■ NS 96 x 96

Steady: Full scale value
Fluctuating: 0.9 x full scale value
Short time: 1.3 x full scale value

■ NS 72 x 72

Steady: 3/4 x full scale value
Fluctuating: 2/3 x full scale value
Short time: Full scale value

#### **Temperature effect**

When the temperature of the measuring system deviates from the reference temperature ( $\pm$ 20 °C): max.  $\pm$ 0.4 %/10 K of full scale value

#### Ingress protection

IP42 per EN/IEC 60529

#### **Process connection**

Copper alloy (> 100 bar stainless steel 316L)
Connection location: ■ Centre back mount

■ Lower back mount (only NS 96 x 96)

NS 96 x 96: G ½ B (male), SW 22 NS 72 x 72: G ¼ B (male), SW 14

#### Pressure element

< 100 bar: Copper alloy, C-type, soft soldered

≥ 100 bar: Stainless steel 316L, helical or spiral type, brazed

#### Movement

Copper alloy, wear parts argentan

#### Dial

Aluminium, white, black lettering

NS 72 x 72 and 96 x 96 with pointer stop pin

#### **Pointer**

Aluminium, black

#### Case / Chassis (DIN 43700)

Steel, galvanised

#### **Basic case**

**Plastic** 

#### Window

Instrument glass

#### Panel frame

Steel, black, narrow, snap-fit

## **Options**

- Other process connection
- Measuring system stainless steel 316L (model 234.11)
- Duplex measuring system max. 60 bar
- Wide panel frame


# **Approvals**


Logo	Description	Country
CE	EU declaration of conformity Pressure equipment directive	European Union
©	GOST (option) Metrology, measurement technology	Russia
6	KazInMetr (option) Metrology, measurement technology	Kazakhstan
-	MTSCHS (option) Permission for commissioning	Kazakhstan
<b>(</b>	BelGIM (option) Metrology, measurement technology	Belarus
	Uzstandard (option) Metrology, measurement technology	Uzbekistan
-	CPA (option) Metrology, measurement technology	China
-	CRN Safety (e.g. electr. safety, overpressure,)	Canada


# **Certificates (option)**

- 2.2 test report per EN 10204 (e.g. state-of-the-art manufacturing, material proof, indication accuracy)
- 3.1 inspection certificate per EN 10204 (e.g. indication accuracy)

### **Dimensions in mm**







NS, connection location	Dimensions in mm									Weight
	b <sub>1</sub>	b <sub>6</sub>	е	f	G	L	1	р□	SW	in kg
96 x 96, lower back mount	44	73	6	30	G ½ B	96	79	88.5	22	0.60
96 x 96, centre back mount	35	47	6	-	G 1/4 B	96	79	88.5	14	0.60
72 x 72, centre back mount	29	42	6	-	G 1/4 B	72	57	66	14	0.30

Process connection per EN 837-1 / 7.3

### **Ordering information**

Model / Nominal size / Scale range / Process connection / Connection location / Options

© 03/2008 WIKA Alexander Wiegand SE & Co. KG, all rights reserved. The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials.

WIKA data sheet PM 02.07 · 10/2020

Page 4 of 4



Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Tel. +49 9372 132-0 Fax +49 9372 132-406

info@wika.de www.wika.de