## Capsule pressure gauge with output signal For the process industry, high overload safety Models PGT63HP.100 and PGT63HP.160

WIKA data sheet PV 16.06













for further approvals see



## **Applications**

- For gaseous, aggressive media, also in aggressive environments
- Measurements of very low pressures from 2.5 mbar
- Output signals 4 ... 20 mA, 0 ... 20 mA, DC 0 ... 10 V for the transmission of process values to the control room

#### Special features

- No configuration necessary due to "plug-and-play"
- High overload safety up to 50 x full scale value
- Easy-to-read analogue display with nominal sizes 100 and 160
- Low measuring error and influence on function from medium pollution
- Measuring chamber protected against unauthorised intervention



intelliGAUGE® model PGT63HP.100

#### Description

Wherever very low pressures have to be indicated locally and, at the same time, a signal transmission to the central control or remote centre is desired, the model PGT63HP intelliGAUGE® (patent, property right: e.g. DE 202007019025) can be used.

The robust capsule measuring system has an overload safety of up to 50 times the full scale value.

An electronic angle encoder, proven in safety-critical automotive applications, determines the position of the pointer shaft - it is a non-contact sensor and therefore completely free from wear and friction. From this, the electrical output signal proportional to the pressure, e.g. 4 ... 20 mA, is produced.

The measuring span (electrical output signal) is adjusted automatically along with the mechanical display, i.e. the scale over the full display range corresponds to 4 ... 20 mA. The electrical zero point can also be set manually.

The electronic WIKA sensor, integrated into the high-quality capsule pressure gauge, combines the advantages of electrical signal transmission with a local mechanical display that remains readable during a power failure.

An additional measuring point for mechanical pressure display can thus be saved.




# **Specifications**

Models PGT63HP.100 and PGT63  Nominal size in mm	■ 100					
Nominai size in mm	■ 160					
Accuracy class	1.6 Option: ■ 1.0 ¹) ■ 0.6 ¹)					
Scale ranges	0 2.5 mbar to 0 100 mbar other units e.g. psi, kPa available or all other equivalent vacuum or combined pressure and vacuum ranges					
Scale	Single scale Option: Dual scale					
Zero point setting	By means of adjustment appliance					
Pressure limitation						
Steady	Full scale value					
Fluctuating	0.9 x full scale value					
Overload safety	50 x full scale value					
	Higher overload safety on request 1)					
Process connection with lower measuring flange	■ G½B ■ ½NPT ■ M20 x 1.5 others on request					
Permissible temperature 2)						
Medium	+100 °C [+212 °F] maximum					
Ambient	-20 +60 °C [-4 140 °F]					
Temperature effect	When the temperature of the measuring system deviates from the reference temperature (+20 $^{\circ}$ C): max. ±0.6 %/10 K of full scale value					
Case	Version S1 per EN 837: With blow-out device in case back					
Case filling	Without					
Wetted materials						
Process connection, media cham- ber, capsule element (pressure element)	Stainless steel 316Ti					
Sealing	PTFE					
Non-wetted materials						
Case, movement, bayonet ring	Stainless steel					
Dial	Aluminium, white, black lettering					
Instrument pointer	Aluminium, black					
Set pointer	Aluminium, red					
Window	Laminated safety glass					
Ingress protection per IEC/EN 60529	IP54					
Mounting	Rigid measuring line Option: Instrument mounting bracket for wall or pipe mounting Mounting flange					

Application test required
 For hazardous areas, the permissible temperatures of the output signal variant 2 will apply exclusively (see page 4). These must not be exceeded at the instrument either (for details see operating instructions). If necessary, measures for cooling (e.g. syphon, instrumentation valve, etc.) have to be taken.

# Design and operating principle

- Pressure-sealed measuring chamber (1) with capsule measuring element
- The capsule element (2) is pressurised from outside and moves in strokes (deflection)
- The deflection is transmitted to the movement (3) and indicated
- The overload safety is achieved through the mutually supporting surfaces of both halves of the capsule element



Models PGT63HP.100 and PGT6	3HP.160					
Output signal	Variant 1: 4 20 mA, 2-wire, passive, per NAMUR NE 43 Variant 2: 4 20 mA, 2-wire, for hazardous areas Variant 3: 0 20 mA, 3-wire Variant 4: 0 10 V, 3-wire					
Supply voltage U <sub>B</sub>	DC 12 V < $U_B \le 30$ V (variant 1 and 3) DC 14 V < $U_B \le 30$ V (variant 2) DC 15 V < $U_B \le 30$ V (variant 4)					
Influence of supply voltage	≤ 0.1 % of full scale/10 V					
Permissible residual ripple of U <sub>B</sub>	≤ 10 % ss					
Permissible max. load R <sub>A</sub>	Variant 1, 2, 3: R <sub>A</sub> $\leq$ (U <sub>B</sub> - 12 V)/0.02 A with R <sub>A</sub> in $\Omega$ and U <sub>B</sub> in V, however max. 600 $\Omega$ Variant 4: R <sub>A</sub> = 100 k $\Omega$					
Effect of load (variant 1, 2, 3)	≤ 0.1 % of full scale					
Impedance at voltage output	0.5 Ω					
Electrical zero point	Through a jumper across terminals 5 and 6 (see operating instructions)					
Long-term stability of electronics	< 0.3 % of full scale per year					
Electr. output signal	≤ 1 % of measuring span					
Linear error	≤ 1 % of measuring span (terminal method)					
Resolution	0.13 % of full scale (10 bit resolution at 360°)					
Refresh rate (measuring rate)	600 ms					
Electrical connection	Cable socket PA 6, black Per VDE 0110 insulation group C/250 V Cable gland M20 x 1.5 Strain relief 6 screw terminals + PE for conductor cross-section 2.5 mm <sup>2</sup>					
Designation of connection terminals, 2-wire (variant 1 and 2)  Designation of connection terminals for 3-wire (variant 3 and 4), see operating instructions	Do not use this  terminal  U <sub>B+</sub> /I+  Terminals 3 and 4: For internal use only Terminals 5 and 6: Reset zero point					

## Safety-related maximum values (variant 2)

Ui	li	Pi	Ci	Li
DC 30 V	100 mA	720 mW	11 nF	negligible

## Permissible temperature ranges (variant 2)

T6	T5	T4 T1
-20 +45 °C	-20 +60 °C	-20 +70 °C
T85°C	T100°C	T135°C
-20 ±45 °C	-20 ±60 °C	-20 ±70 °C

For further information on hazardous areas, see operating instructions.

## **Approvals**

Logo	Description	Country		
<b>€</b>	EU declaration of conformity  ■ EMC directive  ■ Pressure equipment directive  ■ RoHS directive  ■ ATEX directive (option)  Hazardous areas  - Ex ia Gas [II 2G Ex ia IIC T6/T5/T4 Gb]  Dust [II 2D Ex ia IIIB T85°C/T100°C/T135°C Db]	European Union		
IEC TECEX	IECEx (option) Hazardous areas - Ex ia Gas [Ex ia IIC T6/T5/T4 Gb] Dust [Ex ia IIIB T85°C/T100°C/T135°C Db]	International		
ERCEx	EAC (option)  ■ EMC directive  ■ Pressure equipment directive  ■ Low voltage directive  ■ Hazardous areas	Eurasian Economic Community		
©	GOST (option) Metrology, measurement technology	Russia		
-	MTSCHS (option) Permission for commissioning	Kazakhstan		
<b>(</b>	BelGIM (option) Metrology, measurement technology	Belarus		
•	UkrSEPRO (option) Metrology, measurement technology	Ukraine		
<b>(</b>	Ex Ukraine (option) Hazardous areas	Ukraine		
	Uzstandard (option) Metrology, measurement technology	Uzbekistan		
-	CRN Safety (e.g. electr. safety, overpressure,)	Canada		

## **Certificates (option)**

- 2.2 test report per EN 10204 (e.g. state-of-the-art manufacturing, indication accuracy)
- 3.1 inspection certificate per EN 10204 (e.g. indication accuracy)

## Patents, property rights

Pointer measuring instrument with output signal 4 ... 20 mA (patent, property right: e.g. DE 202007019025, US 2010045366, CN 101438333)


Approvals and certificates, see website

#### **Accessories**

- Sealings (model 910.17, see data sheet AC 09.08)
- Valves (models IV20/IV21, see data sheet AC 09.19, and models IV10/IV11, see data sheet AC 09.22)
- Syphons (model 910.15, see data sheet AC 09.06)
- Overpressure protector (model 910.13; see data sheet AC 09.04)
- Cooling element (model 910.32, see data sheet AC 09.21)
- Switch contacts (see data sheet AC 08.01)

## **Dimensions in mm**

## intelliGAUGE® models PGT63HP.100 and PGT63HP.160



NS	Dimensions in mm							Weight in			
	а	b	С	d <sub>1</sub>	D <sub>1</sub>	D <sub>2</sub>	е	G	h ±1	SW	kg
100	25	59.5	94	133	101	99	17	G 1/2 B	170	22	1.6
160	25	65	124	133	161	159	17	G 1/2 B	200	22	2.1

#### **Ordering information**

Model / Nominal size / Scale range / Output signal / Connection location / Process connection / Options

© 09/2008 WIKA Alexander Wiegand SE & Co. KG, all rights reserved. The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials.

WIKA data sheet PV 16.06 · 04/2021

Page 6 of 6



+49 9372 132-406

info@wika.de www.wika.de

Fax