Bourdon tube pressure gauge, copper alloy Stainless steel case, case filling Model 213.53, NS 50 [2"], 63 [2 ½"] and 100 [4"]

WIKA data sheet PM 02.12





for further approvals, see page 7

Applications

- For measuring locations with high dynamic pressure loads and vibrations
- For gaseous and liquid media that are not highly viscous or crystallising and will not attack copper alloy parts
- Hydraulics
- Compressors, shipbuilding

Special features

- Very good vibration and shock resistance
- Especially robust design
- Type approval for the shipbuilding industry
- Scale ranges to 0 ... 1,000 bar or 0 ... 15,000 psi



Bourdon tube pressure gauge, model 213.53.100, lower mount

Description

The liquid-filled model 213.53 mechanical Bourdon tube pressure gauge is constructed with a case from stainless steel and wetted parts from copper alloy.

WIKA manufactures and qualifies the pressure gauge in accordance with the standards EN 837-1 and ASME B40.100. As a safety function, this instrument has a blow-out device. In the event of a failure, overpressure can escape there.

Due to the case filling, the pressure element and movement are efficiently damped. Therefore, these instruments are particularly suited to measuring locations with high dynamic loads, such as fast load cycles or vibrations.

The cases of the model 213.53 are available in nominal sizes of 50 [2"], 63 [2 $\frac{1}{2}$ "] and 100 [4"] and fulfil IP65 ingress protection. With an accuracy of up to class 1.0, this pressure gauge is suitable for a wide range of applications in industry.

For mounting in control panels, the pressure gauges with a back mount process connection can be fitted with a mounting flange or with a triangular profile ring and mounting bracket.



Specifications

Basic information		
Standard	■ EN 837-1 ■ ASME B40.100	
	For information on the "Selection, installation, handling and operation of pressure gauges", see technical information IN 00.05.	
Further version	Special design, mode	1213.57
Nominal size (NS)	■ Ø 50 mm [2"] ■ Ø 63 mm [2 ½"] ■ Ø 100 mm [4"]	
Connection location	 Lower mount (radial) Centre back mount (only for NS 50 [2"] and NS 63 [2 ½"]) Lower back mount (only for NS 100 [4"]) 	
Window	Plastic, crystal-clearLaminated safety glass	
Case		
Design	NS 50 [2"], 63 [2 ½"]	Safety level "S2" per EN 837-1: With blow-out device
	NS 100 [4"]	Safety level "S1" per EN 837-1: With blow-out device
	Position of blow-out device: NS 50 [2"]: Case back, at 12 o'clock NS 63 [2 ½"], 100 [4"]: Case circumference, at 12 o'clock Filling plug can be vented and resealed for internal pressure compensation Sealing towards process connection with O-ring	
Material	Stainless steel, natural finish	
Ring	Crimp ring, stainless steel	
Mounting	 Without Panel mounting flange, stainless steel ¹⁾ Panel mounting flange, polished stainless steel ²⁾ Triangular profile ring with mounting bracket, polished stainless steel ³⁾ Surface mounting flange, stainless steel ⁴⁾ 	
Case filling	 ■ Glycerine ■ Glycerine-water mixture for scale range ≤ 0 2.5 bar [≤ 0 40 psi] ■ Silicone oil 	
Movement	Copper alloy	

Measuring element		
Type of measuring element	Bourdon tube, C-type or helical type	
Material		
NS 50 [2"]	≤ 600 bar	Copper alloy
	> 600 bar	Stainless steel 316L
NS 63 [2 ½"], NS 100 [4"]	≤ 400 bar	Copper alloy
	> 400 bar	Stainless steel 316L
Leak tightness	Leakage rate: < 5 · 10 ⁻³ mbar l/s	

¹⁾ Only for back mount 2) Only for NS 63 [2 $\frac{1}{2}$ "] and NS 100 [4"], back mount 3) Only for NS 63 [2 $\frac{1}{2}$ "] 4) Only for NS 63 [2 $\frac{1}{2}$ "] and NS 100 [4"]

Accuracy specifications		
Accuracy class		
NS 50 [2"], 63 [2 ½"]	■ EN 837-1	Class 1.6
	■ ASME B40.100	$\pm 2~\%$ $\pm 1~\%$ $\pm 2~\%$ of measuring span (grade A)
NS 100 [4"]	■ EN 837-1	Class 1.0
	■ ASME B40.100	±1 % of measuring span (grade 1A)
Temperature error	On deviation from the reference conditions at the measuring system: $\leq \pm 0.4$ % per 10 °C [$\leq \pm 0.4$ % per 18 °F] of full scale value	
Reference conditions		
Ambient temperature	+20 °C [68 °F]	

Scale ranges

bar	
0 0.6	0 30
0 1	0 40
0 1.6	0 60
0 2	070
0 2.5	0 100
0 4	0 140
06	0 160
07	0200
0 10	0 250
0 12	0 315
0 14	0 400
0 16	0 600
0 20	0700
0 25	0 1,000

kg/cm ²	
0 0.6	0 40
0 1	0 60
0 1.6	070
02	0 100
0 2.5	0 140
0 4	0 160
06	0200
07	0 250
0 10	0 315
0 14	0 400
0 16	0 600
0 20	0700
0 25	0 1,000
0 30	

kPa	
060	0 4,000
070	0 6,000
0 100	0 7,000
0 160	0 8,000
0 200	0 10,000
0 250	0 14,000
0 400	0 16,000
0 600	0 20,000
0 700	0 25,000
0 800	0 31,500
0 1,000	0 40,000
0 1,400	0 60,000
0 1,600	0 70,000
0 2,500	0 100,000
0 3,000	

MPa	
0 0.06	0 4
0 0.1	06
0 0.16	07
0 0.2	0 10
0 0.25	0 14
0 0.4	0 16
0 0.6	0 20
0 0.7	0 25
0 1	0 31.5
0 1.4	0 40
0 1.6	0 60
02	0 70
0 2.5	0 100
03	

psi	
0 10	0 600
0 15	0 800
0 30	0 1,000
0 60	0 1,500
0 100	0 2,000
0 150	0 3,000
0 160	0 4,000
0 200	0 5,000
0 300	0 6,000
0 400	0 7.500

Vacuum and +/- scale ranges

bar	
-0.6 0	-1 +9
-1 0	-1 +10
-1 +0.6	-1 +15
-1 +1	-1 +24
-1 +1.5	-1 +25
-1 +2	-1 +30
-1 +3	-1 +32
-1 +4	-1 +40
-1 +7	

kg/cm ²	
-0.6 0	-1 +5
-1 0	-1 +7
-1 +0.6	-1 +9
-1 +1	-1 +10
-1 +1.5	-1 +15
-1 +2	-1 +24
-1 +3	-1 +30
-1 +4	

kPa	
-60 0	-100 +500
-100 0	-100 +700
-100 +60	-100 +900
-100 +100	-100 +1,000
-100 +150	-100 +1,500
-100 +200	-100 +2,400
-100 +300	-100 +3,000
-100 +400	

MPa	
-0.06 0	-0.1 +0.5
-0.1 0	-0.1 +0.9
-0.1 +0.06	-0.1 +1.5
-0.1 +0.15	-0.1 +2.4
-0.1 +0.3	

psi	
-15 inHg 0	-30 inHg +100
-30 inHg 0	-30 inHg +160
-30 inHg +15	-30 inHg +200
-30 inHg +30	-30 inHg +300
-30 inHg +60	

Further details on: Scale ranges				
Special scale ranges	Other scale ranges on request			
Unit	 ■ bar ■ psi ■ kg/cm² ■ kPa ■ MPa 			
Increased overload safety	■ Without ■ 2 times			
	The possibility of selection depends on the scale range			
Dial				
Scale colour	Black			
Material	Aluminium			
Special scale	■ Without■ With temperature scale for refrigerant, e.g. for NH₃: R 717			
	Other scales or customer-specific dials, e.g. with red mark, circular arcs or circular sectors, on request			

Further details on: Scale ranges					
Pointer					
Instrument pointer	Aluminium, black				
Mark pointer/drag pointer	 Without Red mark pointer on dial, fixed Red mark pointer on window, adjustable Mark pointer on bayonet ring, adjustable Red drag pointer on window, adjustable 				
Pointer stop pin	 Without At zero point (only for NS 50 [2"] and NS 63 [2 ½"]) At 6 o'clock (only for NS 100 [4"]) 				

Process connection	
Standard	■ EN 837-1 ■ ISO 7 ■ ANSI/B1.20.1
Size	
EN 837-1	■ G 1/8 B, male thread ■ G 1/4 B, male thread ■ G 1/2 B, male thread ■ M12 x 1.5, male thread ■ M20 x 1.5, male thread
ISO 7	■ R ¼, male thread■ R ½, male thread
ANSI/B1.20.1	 ¼ NPT, male thread ½ NPT, male thread
Restrictor	■ Without ■ Ø 0.5 mm [0.02"], copper alloy ■ Ø 0.3 mm [0.012"], copper alloy
Material (wetted)	
Process connection	Copper alloy
Bourdon tube	→ See table "Measuring element", page 2

Other process connections on request

Operating conditions				
Medium temperature				
Instruments with glycerine filling	-20 +100 °C [-4 +212	2°F]		
Instruments with silicone oil filling	-40 +100 °C [-40 +2	12 °F]		
Ambient temperature				
Instruments with glycerine filling	-20 +60 °C [-4 +140	°F]		
Instruments with silicone oil filling	-40 +60 °C [-40 +140)°F]		
Pressure limitation				
NS 50 [2"], 63 [2 ½"]	Steady	3/4 x full scale value		
	Fluctuating	2/3 x full scale value		
	Short time	Full scale value		
NS 100 [4"]	Steady	Full scale value		
	Fluctuating	0.9 x full scale value		
	Short time	1.3 x full scale value		
Ingress protection per IEC/EN 60529	 IP65 IP66 (only selectable for scale ranges ≥ 0 20 bar [≥ 0 400 psi]) 			

Approvals

Logo	Description	Region		
CE	EU declaration of conformity	European Union		
	Pressure equipment directive PS > 200 bar, module A, pressure accessory			
UK	UKCA	United Kingdom		
CA	Pressure equipment (safety) regulations			
-	CRN Safety (e.g. electr. safety, overpressure,) For scale ranges ≤ 1,000 bar	Canada		

Optional approvals

Logo	Description	Region
6	PAC Kazakhstan Metrology, measurement technology	Kazakhstan
-	MChS Permission for commissioning	Kazakhstan
-	PAC Ukraine Metrology, measurement technology	Ukraine
	PAC Uzbekistan Metrology, measurement technology	Uzbekistan
-	PAC China Metrology, measurement technology	China
(DNV)	DNV GL Ships, shipbuilding (e.g. offshore)	International

Manufacturer's information and certificates


Logo	Description
-	Pressure equipment directive (PED) for maximum allowable pressure PS ≤ 200 bar
-	Suitability of wetted materials for drinking water in accordance with the European 4MS initiative

Certificates (option)

Certificates	
Certificates	 2.2 test report per EN 10204 (e.g. state-of-the-art manufacturing, indication accuracy) 3.1 inspection certificate for indication accuracy per EN 10204 PCA calibration certificate, traceable and accredited in accordance with ISO/IEC 17025 Calibration certificate by a national accreditation body, traceable and accredited in accordance with ISO/IEC 17025 on request
Recommended calibration interval	1 year (dependent on conditions of use)

 $[\]rightarrow$ For approvals and certificates, see website

Dimensions in mm [in]



NS	Weight
NS 50 [2"]	0.15 kg [0.33 lb]
NS 63 [2 ½"]	0.21 kg [0.46 lb]


Process connection with thread per EN 837-1

NS	G	Dimensions in mm [in]						
		h ±1 [0.04]	S3	а	b ±0.5 [0.02]	е	D	sw
50 [2"]	G 1/8 B	45 [1.77]	10 [0.39]	12 [0.47]	30 [1.18]	5.5 [0.22]	55 [2.17]	14 [0.55]
	G 1/4 B	48 [1.89]	13 [0.51]	12 [0.47]	30 [1.18]	5.5 [0.22]	55 [2.17]	14 [0.55]
	M12 x 1.5	48 [1.89]	13 [0.51]	12 [0.47]	30 [1.18]	5.5 [0.22]	55 [2.17]	14 [0.55]
63 [2 ½"]	G 1/8 B	51 [2.01]	10 [0.39]	13 [0.51]	32 [1.26]	6.5 [0.26]	68 [2.68]	14 [0.55]
	G 1/4 B	54 [2.13]	13 [0.51]	13 [0.51]	32 [1.26]	6.5 [0.26]	68 [2.68]	14 [0.55]
	M12 x 1.5	54 [2.13]	13 [0.51]	13 [0.51]	32 [1.26]	6.5 [0.26]	68 [2.68]	14 [0.55]

Process connection with thread per ISO 7

NS	G	Dimensions in mm [in]						
		h ±1 [0.04]	S3	а	b ±0.5 [0.02]	е	D	SW
50 [2"]	R 1/8	45 [1.77]	10 [0.39]	12 [0.47]	30 [1.18]	5.5 [0.22]	55 [2.17]	14 [0.55]
	R 1/4	51 [2.01]	13 [0.51]	12 [0.47]	30 [1.18]	5.5 [0.22]	55 [2.17]	14 [0.55]
63 [2 ½"]	R 1/8	51 [2.01]	10 [0.39]	13 [0.51]	32 [1.26]	6.5 [0.26]	68 [2.68]	14 [0.55]
	R 1/4	54 [2.13]	13 [0.51]	13 [0.51]	32 [1.26]	6.5 [0.26]	68 [2.68]	14 [0.55]

NS	G	Dimensions in mm [in]								
		h ±1 [0.04]	S3	а	b ±0.5 [0.02]	е	D	SW		
50 [2"]	1/8 NPT	45 [1.77]	10 [0.39]	12 [0.47]	30 [1.18]	5.5 [0.22]	55 [2.17]	14 [0.55]		
	1/4 NPT	51 [2.01]	13 [0.51]	12 [0.47]	30 [1.18]	5.5 [0.22]	55 [2.17]	14 [0.55]		
63 [2 ½"]	1/8 NPT	51 [2.01]	10 [0.39]	13 [0.51]	32 [1.26]	6.5 [0.26]	68 [2.68]	14 [0.55]		
	1/4 NPT	54 [2.13]	13 [0.51]	13 [0.51]	32 [1.26]	6.5 [0.26]	68 [2.68]	14 [0.55]		



NS	Weight
NS 100 [4"]	0.8 kg [1.76 lb]


Process connection with thread per EN 837-1

NS	G	Dimensions in mm [in]							
		h ±1 [0.04]	S3	а	b ±0.5 [0.02]	D	sw		
NS 100 [4"]	G 1/4 B	80 [3.15]	13 [0.51]	15.4 [0.61]	48 [1.89]	107 [4.21]	22 [0.87]		
	G 1/2 B	87 [3.43]	20 [0.79]	15.4 [0.61]	48 [1.89]	107 [4.21]	22 [0.87]		

Process connection with thread per ISO 7

NS	G	Dimensions in mm [in]							
		h ±1 [0.04]	S 3	а	b ±0.5 [0.02]	D	SW		
NS 100 [4"]	R 1/4	80 [3.15]	13 [0.51]	15.4 [0.61]	48 [1.89]	107 [4.21]	22 [0.87]		
	R 1/2	86 [3.39]	19 [0.75]	15.4 [0.61]	48 [1.89]	107 [4.21]	22 [0.87]		

NS	G	Dimensions in mm [in]							
		h ±1 [0.04]	S3	а	b ±0.5 [0.02]	D	sw		
NS 100 [4"]	1/4 NPT	80 [3.15]	13 [0.51]	15.4 [0.61]	48 [1.89]	107 [4.21]	22 [0.87]		
	½ NPT	86 [3.39]	19 [0.75]	15.4 [0.61]	48 [1.89]	107 [4.21]	22 [0.87]		



NS	Weight
NS 50 [2½"]	0.15 kg [0.33 lb]
NS 63 [2½"]	0.21 kg [0.46 lb]


Process connection with thread per EN 837-1

NS	G	Dimensions in mm [in]							
		b2 ±0.5 [0.02]	b ±0.5 [0.02]	S 3	е	D	sw		
50 [2"]	G 1/8 B	52 [2.17]	30 [1.18]	10 [0.39]	5.5 [0.22]	55 [2.17]	14 [0.55]		
	G 1/4 B	55 [2.17]	30 [1.18]	13 [0.51]	5.5 [0.22]	55 [2.17]	14 [0.55]		
	M12 x 1.5	55 [2.17]	30 [1.18]	13 [0.51]	5.5 [0.22]	55 [2.17]	14 [0.55]		
63 [2 ½"]	G 1/8 B	54 [2.13]	32 [1.26]	10 [0.39]	6.5 [0.26]	68 [2.68]	14 [0.55]		
	G 1/4 B	57 [2.24]	32 [1.26]	13 [0.51]	6.5 [0.26]	68 [2.68]	14 [0.55]		
	M12 x 1.5	57 [2.24]	32 [1.26]	13 [0.51]	6.5 [0.26]	68 [2.68]	14 [0.55]		

Process connection with thread per ISO 7

NS	G	Dimensions in mm [in]							
		b2 ±0.5 [0.02]	b ±0.5 [0.02]	S3	е	D	sw		
50 [2"]	R 1/8	52 [2.17]	30 [1.18]	10 [0.39]	5.5 [0.22]	55 [2.17]	14 [0.55]		
	R 1/4	55 [2.17]	30 [1.18]	13 [0.51]	5.5 [0.22]	55 [2.17]	14 [0.55]		
63 [2 ½"]	R 1/8	54 [2.13]	32 [1.26]	10 [0.39]	6.5 [0.26]	68 [2.68]	14 [0.55]		
	R 1/4	57 [2.24]	32 [1.26]	13 [0.51]	6.5 [0.26]	68 [2.68]	14 [0.55]		

NS	G	Dimensions in mm [in]							
		b2 ±0.5 [0.02]	b ±0.5 [0.02]	S3	е	D	sw		
50 [2"]	1/8 NPT	52 [2.17]	30 [1.18]	10 [0.39]	5.5 [0.22]	55 [2.17]	14 [0.55]		
	1/4 NPT	55 [2.17]	30 [1.18]	13 [0.51]	5.5 [0.22]	55 [2.17]	14 [0.55]		
63 [2 ½"]	1/8 NPT	54 [2.13]	32 [1.26]	10 [0.39]	6.5 [0.26]	68 [2.68]	14 [0.55]		
	1/4 NPT	57 [2.24]	32 [1.26]	13 [0.51]	6.5 [0.26]	68 [2.68]	14 [0.55]		



NS	Weight
NS 100 [4"]	0.8 kg [1.76 lb]

Process connection with thread per EN 837-1

NS	G	Dimensions in mm [in]							
		b2 ±0.5 [0.02]	b ±0.5 [0.02]	S3	е	f	D	SW	
NS 100	G 1/4 B	76.5 [3.01]	50 [1.97]	13 [0.51]	9 [0.36]	30 [1.18]	107 [4.21]	22 [0.87]	
[4"]	G 1/2 B	83.5 [3.29]	50 [1.97]	20 [0.97]	9 [0.36]	30 [1.18]	107 [4.21]	22 [0.87]	

Process connection with thread per ISO 7

NS	G	Dimensions in mm [in]							
		b2 ±0.5 [0.02]	b ±0.5 [0.02]	S3	е	f	D	SW	
NS 100	R 1/4	76.5 [3.01]	50 [1.97]	13 [0.51]	9 [0.36]	30 [1.18]	107 [4.21]	22 [0.87]	
[4"]	R 1/2	82.5 [3.25]	50 [1.97]	20 [0.97]	9 [0.36]	30 [1.18]	107 [4.21]	22 [0.87]	

NS	G	Dimensions in mm [in]						
		b2 ±0.5 [0.02]	b ±0.5 [0.02]	S3	е	f	D	SW
NS 100 [4"]	1/4 NPT	76.5 [3.01]	50 [1.97]	13 [0.51]	9 [0.36]	30 [1.18]	107 [4.21]	22 [0.87]
	½ NPT	82.5 [3.25]	50 [1.97]	20 [0.97]	9 [0.36]	30 [1.18]	107 [4.21]	22 [0.87]

Ordering information

Model / Nominal size / Scale range / Process connection / Connection location / Options

© 09/2008 WIKA Alexander Wiegand SE & Co. KG, all rights reserved.

The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials.

WIKA data sheet PM 02.12 · 03/2023

Page 12 of 12



WIKA Alexander Wiegand SE & Co. KG Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Tel. +49 9372 132-0 info@wika.de www.wika.de