Differential pressure gauge with electrical output signal Model A2G-15

WIKA data sheet PV 17.40









for further approvals see



Applications

- Differential pressure monitoring for filters
- Pressure monitoring for ventilators
- Overpressure monitoring for clean rooms and also under- and overpressure monitoring for laboratories and operating rooms

Special features

- Electrical output signal DC 0 ... 10 V (3-wire) or 4 ... 20 mA (2-wire)
- Simple and fast mounting via threaded bezel
- Separated construction of measuring chamber and display area
- Integrated sealing element for direct mounting in a ventilation duct or instrument panel
- Available as a built-in or add-on version



Differential pressure gauge with electrical output signal, add-on version, model A2G-15

Description

The model A2G-15 differential pressure gauge with electrical output signal is used for monitoring the differential pressure in ventilation and air-conditioning applications. The measuring ranges cover from 0 ... 100 Pa to 0 ... 6,000 Pa. Plus/minus ranges can be fulfilled from -50 ... +50 Pa to -1,500 ... +1,500 Pa.

Electrical output signals for both measurands (DC 0 ... 10 V or 4 ... 20 mA) enable the direct connection to control systems or the building automation system.

The separated construction of the measuring chamber and display area ensures that impurities from the process air do not settle on the back of the window.

The differential pressure gauge is available in IP54 and IP65 ingress protection as well as two different mounting versions.

Built-in version

The built-in version with threaded bezel is notable for its fast and tool-free mounting. The built-in case features two back mount connections with a G ½ female thread, into which matching threaded pressure connections are screwed.

Add-on version

With the add-on version, the add-on case is attached with three screws and then the pressure measuring system is fitted into the case. The add-on case features two lower-mount connections with a G 1/8 female thread, into which matching threaded pressure connections are screwed. The position of each connection can be altered through 90° by rotating the add-on case.

WIKA data sheet PV 17.40 · 05/2020


Page 1 of 5



Specifications

Differential pressure gauge with electrical output signal, model A2G-15				
Version	■ Standard version			
	Silicone-free version			
Nominal size in mm	110			
Measuring range	■ 0 100 Pa to 0 6,000 Pa ■ -50 +50 Pa to -1,500 +1,500 Pa Other plus/minus ranges on request			
Unit	 Pa kPa inWC mmWC mbar 			
Scale	Single scaleDual scale			
Accuracy class				
Span ≥ 250 Pa	3.0			
Span 101 249 Pa	5.0			
Span ≤ 100 Pa	10.0			
Process connection	G $\frac{1}{8}$ female Threaded pressure connectionfor measuring hoses with inner diameter 4 6 mm (see "Accessories")			
Movement	Contact-free transmission (SWISS MOVEMENT)			
Output signal	■ DC 0 10 V, 3-wire ■ 4 20 mA, 2-wire			
Supply voltage U _B	DC 15 35 V			
Electrical connection	Cable gland M12			
Materials				
Case components	Plastic, glass-fibre reinforcedWithout			
Separating diaphragm	SiliconeEPDM (with silicone-free version)			
Window	Polycarbonate (UV stabilised)			
Dial	Aluminium			
Pointer	Plastic, black			
Mark pointer	■ Without ■ Plastic, red			
Medium	AirNon-flammable and non-aggressive gases			
Permissible temperature				
Medium	-16 +50 °C [-3 +122 °F]			
Ambient	-30 +80 °C [-22 +176 °F]			
Max. working pressure (static pressure)	20 kPa			
Ingress protection per IEC/EN 60529	■ IP54 ■ IP65			
Weight (pressure measuring system)	255 g			

Electrical connection





Approvals (option)

Logo	Description	Country
ERE	EAC Import certificate	Eurasian Economic Community
©	GOST Metrology, measurement technology	Russia
6	KazInMetr Metrology, measurement technology	Kazakhstan
-	MTSCHS Permission for commissioning	Kazakhstan
•	UkrSEPRO Metrology, measurement technology	Ukraine


Certificates (option)

- Measurement report per EN 837
- 2.2 test report per EN 10204
- 3.1 inspection certificate per EN 10204

Approvals and certificates, see website

Mounting versions

Built-in version 1)




1) For wall thicknesses 1 \dots 70 mm


Legend


- ① Pressure measuring system
- ② Red mark pointer
- 3 Built-in case
- Threaded bezel
- S Cable gland
- 6 Add-on case

Add-on version



Dimensions in mm





Legend

Variant 1: With threaded pressure connection, straight,

Ø 4 ... 6 mm

Variant 2: With threaded pressure connection, angled,

Ø 4 ... 6 mm

Accessories

Description		Order number
	Process connections	
	2 x threaded pressure connection, straight, Ø 4 6 mm	40423607
-	2 x threaded pressure connection, angled, Ø 4 6 mm	40423526
	With mounting thread G 1/8 for pipes 6.35 mm/1/4"	40232867
	Combi hose connection for pressure measuring hoses Ø 4 7 mm	40232484
-\$	Static duct probes with combi hose connection for pressure measuring hoses Ø 4 \dots 7 mm	
V	Insertion length 100 mm	40232981
	Insertion length 150 mm	40232999
	Insertion length 200 mm	40233006
	Measuring hoses	
	PVC hose, inner diameter 4 mm, roll at 25 m	40217841
	PVC hose, inner diameter 6 mm, roll at 25 m	40217850
	Silicone hose, inner diameter 4 mm, roll at 25 m	40208940
	Silicone hose, inner diameter 6 mm, roll at 25 m	40208958
1	Duct connectors for measuring hoses Ø 4 6 mm	40217507
	Weather protection	40241564

Ordering information

Model / Version / Measuring range / Output signal / Unit / Scale / Ingress protection / Mark pointer / Mounting version / Accessories / Approvals / Certificates / Options

© 09/2008 WIKA Alexander Wiegand SE & Co. KG, all rights reserved.

The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials.

WIKA data sheet PV 17.40 \cdot 05/2020

Page 5 of 5



Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Tel. +49 9372 132-0 Fax +49 9372 132-406

info@wika.de www.wika.de