Capsule pressure gauge, stainless steel For the process industry, high overload safety Model 632.51, NS 100 [4"] and 160 [6"]

WIKA data sheet PM 06.06





for further approvals, see page 6

Applications

- Pressure measurement at very low pressures
- For gaseous, aggressive media, also in aggressive environments
- Robust design and ingress protection IP54, suitable for outdoor use

Special features

- High overload safety up to 50 x full scale value
- Scale ranges from 0 ... 2.5 mbar
- Measuring chamber protected against unauthorised intervention
- Low measured error and influence on function from medium pollution




Capsule pressure gauge, model 632.51

Description

These capsule pressure gauges are used when extremely-low pressures must be displayed on site. The instruments can be overloaded up to 50 times the full scale value without any problems.

The large effective area of the two welded, radially corrugated diaphragms of the capsule element allows the reliable measurement of the smallest pressures. These measuring instruments, made entirely of stainless steel, are suitable for gaseous, aggressive media.

The capsule pressure gauge of model 632.51 has been qualified and manufactured in accordance with EN 837-3.





Data sheets showing similar products: Capsule pressure gauge with switch contacts; model 632.51+8xx; see data sheet PV 26.06 Capsule pressure gauge, copper alloy; model 612.20; see data sheet PM 06.02



The pressure element, the capsule element, consists of two radially corrugated diaphragms welded at the edge. This increases the effective area of the pressure element compared to diaphragm pressure gauges. Capsule pressure gauges are therefore able to measure extremely low pressures.

The pressure element shown above consists of 3 capsule elements. The link passes through the centre and is attached to the lower capsule element so that unhindered deformation is possible in the media chamber. The pressure element is pressurised from the outside. This results in stroke movements - the measuring travel itself. The measuring travel of the pressure element is transmitted to the movement via the link and displayed by the instrument pointer on the dial.

Overload safety

The capsule element can, through the mutually supporting surfaces of both halves of the capsule element, withstand up to 50 times overload. With a scale range of 0 ... 2.5 mbar, a short-term overpressure of up to 125 mbar is not problematic; the accuracy is not affected.

Specifications

Basic information		
Standard		
Diaphragm and capsule pressure gauges	EN 837-3	
→ For information on the "Selection, installation, handling and operation of pressure gauges", see Technical information IN 00.05.		
Nominal size (NS)	 Ø 100 mm [4"] Ø 160 mm [6"] 	
Window	Laminated safety glass	
Case	Safety level "S1" per EN 837-1: With blow-out device	
Material	 Stainless steel 1.4301 (304) Stainless steel 1.4571 (316 Ti) 	
Ring	Bayonet ring, stainless steel	
Movement	Stainless steel	

Measuring element	
Type of measuring element	Capsule element
Materials (wetted)	
Capsule element	Stainless steel 1.4571 (316 Ti)
Measuring chamber	Stainless steel 1.4571 (316 Ti)
Sealing	PTFE
Process connection	Stainless steel 1.4571 (316 Ti)

Accuracy specifications	
Accuracy class	 1.6 1.0¹⁾ 0.6¹⁾
Zero point setting	Setting by means of adjustable pointer
Temperature error	On deviation from the reference conditions at the measuring system: $\le \pm 0.6$ % per 10 °C [$\le \pm 0.6$ % per 18 °F] of full scale value
Reference conditions	
Ambient temperature	+20 °C [68 °F]

1) Application test required

Scale ranges

mbar	
02,5	025
04	0 40
06	0 60
0 10	0 100
0 16	-

mmH ₂ O	
025	0250
040	0400
060	0600
0 100	0 1,000
0 160	-

inH ₂ O	
05	0 25
0 10	0 30
0 15	0 40
0 20	-

kPa	
0 1	04
0 1,6	06
0 2,5	0 10

Vacuum and +/- scale ranges

mbar	
-2.5 0	-8 +8
-4 0	-10 +6
-6 0	-10 +15
-10 0	-10 +30
-16 0	-10 +50
-25 0	-15 +10
-40 0	-15 +25
-60 0	-20+5
-100 0	-20 +20
-1+5	-20 +40
-2 +4	-25 +15
-2 +8	-25 +75
-3 +3	-30 +30
-4 +2	-40 +20
-4 +6	-40 +60
-4 +12	-50 +10
-5 +1	-50 +50
-5 +5	-60 +40
-6+10	-75 +25
-8 +2	-80 +20

Other scale ranges on request

Further details on: Scale ranges			
Unit	 mbar kPa mmH₂O inH₂O 		
	Other units on request		
Overload safety	50 x full scale value 1) 2)		
Vacuum resistance	 Without 10 x full scale value²⁾ 3 x full scale value²⁾ 		
Dial			
Scale layout	Single scaleDual scale		
Scale colour	Single scale	Black	
	Dual scale	Black/red	
Material	Aluminium		
Customer-specific version	Other scales, e.g. with red mark, circular arcs or circular sectors, on request → Alternatively, adhesive label set for red and green circular arcs; see data sheet AC 08.03		
Instrument pointer	Adjustable poir	Adjustable pointer, aluminium, black	

Higher overload safety possible in certain circumstances after application test
 For vacuum and +/- scale ranges different specifications for overload safety/vacuum resistance apply

Process connection	
Standard	 EN 837 ANSI / ASME B1.20.1
Size 1)	
EN 837	 G ½ B M20 x 1.5
ANSI / ASME B1.20.1	½ NPT
Materials (wetted)	
Capsule element	Stainless steel 1.4571 (316 Ti)
Measuring chamber	Stainless steel 1.4571 (316 Ti)
Sealing	PTFE
Process connection	Stainless steel 1.4571 (316 Ti)

1) For further connection threads \rightarrow See data sheet IN 00.10

Other process connections on request

Operating conditions	
Medium temperature range	+100 °C [+212 °F] maximum
Ambient temperature range	-20 +60 °C [-4 +140 °F]
Storage temperature range	-40 +70 °C [-4 140 °F]
Pressure limitation	
Steady	Full scale value
Fluctuating	0.9 x full scale value
Ingress protection per IEC/EN 60529	IP54

Other versions

- Version for hazardous areas (Ex h)
- Capsule pressure gauge with switch contacts; see data sheet PV 26.06
- Capsule pressure gauge with output signal, see data sheet PV 16.06
- Oil- and grease-free
- For oxygen, oil- and grease-free
- With pre-volume deflagration flame arrester ¹⁾ for connection to zone 0 (EPL Ga); model 910.21; see data sheet AC 91.02

1) Only for instruments with Ex approval

Approvals

Logo	Description	Region
-	CRN	Canada
	Safety (e.g. electr. safety, overpressure,)	

Optional approvals

Logo	Description	Region	
€€	EU declaration of conformity ATEX directive Hazardous areas Gas II 2G h IIC T6 T1 Gb X Dust II 2D h IIIC T85°C T450°C Db X	European Union	
UK CA	UKCA Equipment and protective systems intended for use in potentially explosive atmospheres regulations	United Kingdom	
EHLEX	EAC Hazardous areas	Eurasian Economic Community	
æ	Ex Ukraine Hazardous areas	Ukraine	
B	PAC Kazakhstan Metrology, measurement technology	Kazakhstan	
-	MChS Permission for commissioning	Kazakhstan	
-	PAC Ukraine Metrology, measurement technology	Ukraine	
Ø	PAC Uzbekistan Metrology, measurement technology	Uzbekistan	
-	PAC China Metrology, measurement technology	China	


Certificates (option)

Certificates	
Certificates	 2.2 test report per EN 10204 (e.g. state-of-the-art manufacturing, indication accuracy) 3.1 inspection certificate per EN 10204 (e.g. material proof for wetted metal parts, indication accuracy)
Recommended calibration interval	1 year (dependent on conditions of use)

For approvals and certificates, see website

Dimensions in mm [in]

Model 632.51



Nominal size 100 [4"]

	Dimensio	Weight in kg							
connection G	d	а	b	D1	D2		h ± 1 [0.04]	SW	[lb]
G ½ B	133 [5.24]	15.5 [0.61]	49.5 [1.95]	101 [3.98]	99 [3.90]	17.5 [0.69]	170 [6.69]	22 [0.87]	1.6 [3.53]
½ NPT	133 [5.24]	15.5 [0.61]	49.5 [1.95]	101 [3.98]	99 [3.90]	17.5 [0.69]	169 [6.65]	22 [0.87]	2.1 [4.63]

Nominal size 160 [6"]

Process	Dimensio	Weight in kg							
connection G	d	а	b	D1	D2	-	h ± 1 [0.04]	SW	[lb]
G ½ B	133 [5.24]	15.5 [0.61]	49.5 [1.95]	161 [6.34]	159 [6.26]	17.5 [0.69]	200 [7.87]	22 [0.87]	1.6 [3.53]
½ NPT	133 [5.24]	15.5 [0.61]	49.5 [1.95]	161 [6.34]	159 [6.26]	17.5 [0.69]	199 [7.83]	22 [0.87]	2.1 [4.63]

Accessories and spare parts

Model		Description	Order number	
Le La C	910.33	Adhesive label set for red and green circular arcs \rightarrow See data sheet AC 08.03	-	
		NS 100 [4"]	14238945	
her all		NS 160 [6"]	14228352	
ಁೢೲ	910.17	Sealings → See data sheet AC 09.08	On request	
	910.14	Connection adapters for pressure measuring instruments → See data sheet AC 09.05	On request	
2 P	910.15	Syphons → See data sheet AC 09.06	On request	
	IV20, IV21	Block-and-bleed valve → See data sheet AC 09.19	On request	
IBF2, IBF3		Monoblock with flange connection → See data sheet AC 09.25	On request	
	910.16	Mounting parts for wall and pipe mounting Instrument mounting bracket and adapter piece → See data sheet AC 09.07	On request	

Ordering information

Model / Nominal size / Scale range / Process connection / Options

© 08/2009 WIKA Alexander Wiegand SE & Co. KG, all rights reserved. The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials. In case of a different interpretation of the translated and the English data sheet, the English wording shall prevail.

WIKA data sheet PM 06.06 · 11/2023



WIKA Alexander Wiegand SE & Co. KG Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Tel. +49 9372 132-0 info@wika.de www.wika.de

Page 8 of 8