Bimetal Thermometer, Process Grade - All Stainless Steel Construction Type TI.50, 5" Dial Size - Back Connected

Datasheet TI.50

# **Applications**

- General process instrumentation in the chanical, petrochemical, oil and gas, energy and water/wastewater industries
- Temperature measurement in harsh and agressive environments
- With liquid dampening suitable for applications with high vibrations

## **Product features**

- Process grade design
- Back connection with external reset
- All stainless steel construction
- Hermetically sealed per ASME B40.3
- Accurate to 1% of full scale value
- Available with silicone case filling for vibration

## Standard version

#### Sizes

5" (127 mm) - Type TI.50

## **Accuracy**

+ 1.0% full scale value per ASME B40.3, Grade A

#### Ranges

From -100°F (70°C) to 1000°F (540°C) From -50°C to 550°C (as single scale) See table on page 2

## **Working Range**

Steady: full scale value

Short time: 110% of full scale value

## **Over/Under Range Protection**

 $\leq$  +500 °F (+260 °C): Temporary up to 50% of full scale > +500 °F (+260 °C): Continuous to 800 °F (+427 °C) Intermittant up to 1000 °F (+538 °C)

## Connection

Material: 304 stainless steel Center back mount (CBM), 1/2" NPT

## Stem

Material: 304 stainless steel Diameter: ¼" (6.35 mm)

Length: 2 1/2" to 72" (63.5 mm to 1,828.8 mm)

## **Measuring Element**

Bi-metal helix



#### Thermometer TI.50

#### Case

Material: 304 stainless steel Hermetically sealed per ASME B40.3 standard Weather protection NEMA 4X (IP 66) External reset slotted hex head on back of case

#### Dial

White aluminum, dished, with black markings

## **Pointer**

Black aluminum

## **Dampening**

Inert gel to minimize pointer oscillation

## **Standard Scales**

Single: Fahrenheit or Celsius

Dual: Fahrenheit (outer) and Celsius (inner)

## **Window Gasket**

Neoprene

Silicone for ranges -100 °F (-70 °C) and ranges > +550 °F (+260 °C)

## Window

Flat instrument glass

## Weight

16 oz. (453 g) - 5" dial

Add 1 oz. (28 g) for every 2" (50 mm) of stem length

## Warranty

7- Year Warranty

Datasheet TI.50 · 6/2015 Page 1 of 2




# **Optional Extras**

- Thermowells
- Silicone fill
- Dampened Movement
- Special scales and dial markings
- Acrylic and safety glass windows
- Calibration certification traceable to NIST
- Min/max pointer
- DIN standards

STANDARD RANGES				
Fahrenheit Single Scale	Dual Scale F & C F Outer, C Inner	Celsius Single Scale		
-100/150 F	-100/150 F & -70/70 C	-50/50 C		
-40/120 F	40/120 F & -40/50 C	-20/120 C		
0/140 F	0/140 F & -20/60 C	0/50 C <sup>1</sup>		
0/200 F	0/200 F & -15/90 C	0/100 C		
0/250 F	0/250 F & -20/120 C	0/150 C		
20/240 F	20/240 F & -5/115 C	0/200 C		
25/125 F	25/125 F & -5/50 C	0/250 C		
50/300 F	50/300 F & 10/150 C	0/300 C		
50/400 F	50/400 F & 10/200 C	0/450 C <sup>1</sup>		
50/550 F	50/500 F & 10/260 C	100/550 C <sup>1</sup>		
150/750 F	150/750 F & 65/400 C			
200/1000 F <sup>1</sup>	200/1000 F & 100/540 C <sup>1</sup>			

<sup>&</sup>lt;sup>1</sup> Not recommended for continous service over 800°F (425°C)

# **Dimensions**



WIKA Type	DIAL SIZE	Α	В	S (Stem Length)
50	5" (127 mm)	5-1/4" (133.4 mm)	15/16" (23.8 mm)	As Specified

Note: Thermowells for temperature instruments are recommended for all process systems where pressure, velocity, or viscous, abrasive and corrosive materials are present individually or in combination. A properly selected thermowell protects the temperature instrument from possible damage resulting from these process variables. Furthermore, a thermowell permits removal of the temperature instrument for replacement, repair or testing without effecting the process media or the system.

#### Ordering information

State computer part number (if available) /type number/size/range/connection size and locations/options required. WIKA reserves the right to make changes without prior notice.

Page 2 of 2 Datasheet TI.50⋅ 6/2015



**WIKA Instrument Corporation** 

1000 Wiegand Boulevard Lawrenceville, GA 30043 1-888-WIKA-USA /770-513-8200 (in GA) Fax 770-338-5118 info@wika.com www.wika.com