Bimetal Thermometer - Industrial Grade - All Stainless Steel Construction Type TI.20, 2" Dial Size - Back Connected

Datasheet TI.20

Applications

- A wide range of applications including machine building, vessels, micro-brewing, boilers and water systems/piping
- Heating and air-conditioning technology (HVAC)
- Temperature measurement in harsh and agressive environments

Product features

- Back connection with external reset
- Robust industrial design
- All stainless steel case construction
- NSF approval available



Thermometer TI.20

Specifications

Size

2" (50.8 mm) - Type TI.20

Accuracy

± 1.0% full scale value per ASME B40.3 Grade A

Min./Max. Ranges

From -100°F (-70°C) to +1000°F (+540°C) From -50°C to +550°C (as single scale) Reference table on page 2

Working Range

Steady: full scale value

Short time: 110% of full scale value

Over/Under Range Protection

 \leq +500 °F (+260 °C): Temporary up to 50% of full scale > +500 °F (+260 °C): Continuous to 800 °F (+427 °C) Intermittant up to 1000 °F (+538 °C)

Connection

Material: 304 stainless steel Center back mount (CBM) 1/4" NPT

Stem

Material: 304 stainless steel Diameter: ¼" (6.35 mm)

Length: 21/2" to 24" (63.5 mm to 609.6 mm)

Measuring Element

Bi-metal helix

Case

Material: 304 stainless steel; hermetically sealed per ASME B40.3 standard

Dial

White aluminum, dished, with black markings

Pointer

Black aluminum

Standard Scales

Single: Fahrenheit or Celsius

Dual: Fahrenheit (outer) and Celsius (inner)

Window

Flat instrument glass

Weight

5 oz. (142 g), 2" (50 mm) dial;

Add 1 oz. (28 g) for every 2" (50 mm) of stem length

Dampening

Inert gel to minimize pointer oscillation

Order Options (min. order may apply)

Special scales and dial markings; Acrylic windows Calibration certification traceable to NIST

Warranty

Limited one year warranty as stated in WIKA's Terms & Conditions of Sale


Datasheet TI.20 · 6/2015 Page 1 of 2



STANDARD RANGES				
Fahrenheit Single Scale	Dual Scale F & C F Outer, C Inner	Celsius Single Scale		
-100/150 F	-100/150 F & -70/70 C	-50/50 C		
-40/120 F	40/120 F & -40/50 C	-20/120 C		
0/140 F	0/140 F & -20/60 C	0/50 C		
0/200 F	0/200 F & -15/90 C	0/100 C		
0/250 F	0/250 F & -20/120 C	0/150 C		
20/240 F	20/240 F & -5/115 C	0/200 C		
25/125 F	25/125 F & -5/50 C ¹	0/250 C		
50/300 F	50/300 F & 10/150 C	0/300 C		
50/400 F	50/400 F & 10/200 C	0/450 C ¹		
50/550 F	50/500 F & 10/260 C	100/550 C ¹		
150/750 F	150/750 F & 65/400 C			
200/1000 F ¹	200/1000 F & 100/540 C ¹			

 $^{^{1}\,\}text{Not}$ recommended for continous service over 800°F (425°C)

Dimensions



WIKA TYPE	DIAL SIZE	Α	В	С	S (STEM LENGTH)
20	2" (50.8 mm)	2-1/16" (52.4 mm)	7/16" (11.1 mm)	1/4" (6.4 mm)	As Specified

Note: Thermowells for temperature instruments are recommended for all process systems where pressure, velocity, or viscous, abrasive and corrosive materials are present individually or in combination. A properly selected thermowell protects the temperature instrument from possible damage resulting from these process variables. Furthermore, a thermowell permits removal of the temperature instrument for replacement, repair or testing without effecting the process media or the system.

Ordering information

State computer part number (if available) /type number/size/range/connection size and locations/options required. WIKA reserves the right to make changes without prior notice.

Page 2 of 2 Datasheet Tl.20 · 6/2015



WIKA Instrument Corporation

1000 Wiegand Boulevard Lawrenceville, GA 30043 1-888-WIKA-USA /770-513-8200 (in GA) Fax 770-338-5118 info@wika.com www.wika.com