Bimetal Thermometer, Industrial Grade - All Stainless Steel Construction Type TI.34 - 3" Dial Size, Bottom Connected

Datasheet TI.34

Applications

- A wide range of applications including machine building, vessels, micro-brewing, boilers and water systems/piping
- Heating and air-conditioning technology (HVAC)
- Temperature measurement in harsh and agressive environments

Product features

- Robust industrial design
- Lower (bottom) connection without external reset
- NEMA 4X (IP 66) weather protection

Specifications

Size

3" (76.2 mm)

Accuracy

± 1.0% full scale value (ASME B40.3)

Ranges

From -100°F (70°C) to 1000°F (540°C) From -50°C to 550°C (as single scale) See table on page 2

Working Range

Steady: full scale value
Short time: 110% of full scale value

Over/Under Range Protection

 \leq +500 °F (+260 °C): Temporary up to 50% of full scale > +500 °F (+260 °C): Continuous to 800 °F (+427 °C) Intermittant up to 1000 °F (+538 °C)

Connection

Material: 304 stainless steel Lower mount (LM), 1/2" NPT

Stem

Material: 304 stainless steel Diameter: ¼" (6.35 mm)

Length: 21/2" to 24" (63.5 mm to 609.6 mm)

Measuring Element

Bi-metal helix

Dial

White aluminum, dished, with black markings



Thermometer TI.34

Case

Material: 304 stainless steel Hermetically sealed Weather protection NEMA 4X (IP 66)

Pointer

Black aluminum

Standard Scales

Single: Fahrenheit or Celsius

Dual: Fahrenheit (outer) and Celsius (inner)

Window Gasket

Neoprene Silicone for ranges -100 $^{\circ}$ F (-70 $^{\circ}$ C) and ranges > +550 $^{\circ}$ F (+260 $^{\circ}$ C)

Window

Flat instrument glass

Weight

11 oz. (311 g) - Type Tl.34 Add 1 oz. (28 g) for every 2" (50 mm) of stem length

Dampening

Inert gel to minimize pointer oscillation

Warranty

Limited one year warranty as stated in WIKA's Terms &

Conditions of Sale

Datasheet TI.34 · 6/2015 Page 1 of 2




Optional Extras

- Thermowells
- Special scales and dial markings
- Acrylic and safety glass windows
- Calibration certification traceable to NIST

STANDARD RANGES					
Fahrenheit Single Scale	Dual Scale F & C F Outer, C Inner	Celsius Single Scale			
-100/150 F	-100/150 F & -70/70 C	-50/50 C			
-40/120 F	40/120 F & -40/50 C	-20/120 C			
0/140 F	0/140 F & -20/60 C	0/50 C ¹			
0/200 F	0/200 F & -15/90 C	0/100 C			
0/250 F	0/250 F & -20/120 C	0/150 C			
20/240 F	20/240 F & -5/115 C	0/200 C			
25/125 F ¹	25/125 F & -5/50 C ¹	0/250 C			
50/300 F	50/300 F & 10/150 C	0/300 C			
50/400 F	50/400 F & 10/200 C	0/450 C ²			
50/550 F	50/500 F & 10/260 C	100/550 C ²			
150/750 F	150/750 F & 65/400 C				
200/1000 F ²	200/1000 F & 100/540 C ²				

¹ Minimum length 4" for Type 34 ² Not recommended for continous service over 800°F (425°C)



Stem Length				
2½" (63.5 mm)				
4" (101.6 mm)				
6" (152.4 mm)				
9" (228.6 mm)				
12" (304.8 mm)				
15" (381.0 mm)				
18" (457.2 mm)				
24" (609.6 mm)				

WIKA Type	DIAL SIZE	Α	В	S (Stem Length)
34	3" (76.2 mm)	3-1/4" (82.6 mm)	1-7/8" (47.6 mm)	As Specified

Note: Thermowells for temperature instruments are recommended for all process systems where pressure, velocity, or viscous, abrasive and corrosive materials are present individually or in combination. A properly selected thermowell protects the temperature instrument from possible damage resulting from these process variables. Furthermore, a thermowell permits removal of the temperature instrument for replacement, repair or testing without effecting the process media or the system.

State computer part number (if available) /type number/size/range/connection size and locations/options required. WIKA reserves the right to make changes without prior notice.

Page 2 of 2 Datasheet TI.34 · 6/2015



WIKA Instrument Corporation

1000 Wiegand Boulevard Lawrenceville, GA 30043 1-888-WIKA-USA /770-513-8200 (in GA) Fax 770-338-5118 info@wika.com www.wika.com