

Thermowells

Fabricated, with Flange

per WIKA Standard • Model SW500F

Thermometers

Application

The thermowells model SW500F are flange-fitted into the process. They are suitable for low and medium process loads, that might occur as a result of flow, temperature and process pressure influences or vibrations.

Standard features

Thermowell material

Stainless steel 1.4571

Flange

per DIN 2527 with sealing face Form C per DIN 2526 per ASME B16.5 with sealing face Form RF

Nominal diameter

per DIN: DN 25, DN 40, DN 50

per ASME: 1", 11/2"

Pressure rating

per DIN: PN 16-40

per ASME: 150 lbs, 300 lbs, 600 lbs

Instrument connection

Female thread G $\frac{1}{2}$, $\frac{1}{2}$ NPT

Bore size

 $\varnothing\,7\,mm,\;\varnothing\,9\,mm,\;\varnothing\,11\,mm,\;\varnothing\,12.2\,mm$

Insertion length U₁

100, 160, 200, 250, 300, 400, 500 mm

Total length L

Insertion length + 45 mm

Maximum process temperature 1)

600 °C with thermowell material stainless steel 1.4571

Maximum process pressure (static) 1)

40 bar with thermowell material stainless steel 1.4571

Optional extras


- Other dimensions and materials
- Quality certificates
- Wake frequency calculations according to Dittrich / Klotter are recommended in critical applications. WIKA offer this as an engineering service.

Following process data are necessary for the calculation:

- Process pressure (in bar or psi)
- Process temperature (in °C or °F)
- Flow rate (in m/s)
- Density (in kg/m³)
- Dimensions and material of thermowell
- 1) Ratings depends on below parameters:
 - Process medium
 - Process pressure and temperature
- Flow rate
- Flow rate- Design of thermowell (dimensions, material)







3709 694.01

Legend:

H₁ Bore depth for female thread

H₂ Length of female thread

L Total length

N Instrument connection

S Wall thickness

S₁ Tip thickness

T Connection length

 U_1 Insertion length

 $Ød_1$ Bore size

 \emptyset F_1 Thermowell outer diameter

Dimensions in mm								Weight in kg (flange DN25 PN16-40)	
N	Ød ₁	Ø F ₁	H ₁	H ₂	S	S ₁	Т	$U_1 = 100 \text{ mm} \ U_1 = 500 \text{ mm}$	
G ½	7	12			2.5	3.5	45	1.470	1.710
	9				1.5	2.5		1.450	1.610
		15	19	15	3	4		1.500	1.860
	11				2	3		1.480	1.740
	12.2				1.4	2.5		1.460	1.620
½ NPT	7	12	_	-	2.5	3.5		1.470	1.710
	9				1.5	2.5		1.450	1.610
		15			3	4		1.500	1.860
	11				2	3		1.480	1.740
	12.2				1.4	2.5		1.460	1.620

additional weight with other flange							
in kg							
DN40	PN16-40	0.760					
DN50	PN16-40	1.630					
	150 lbs	-0.460					
1"	300 lbs	0.040					
	600 lbs	0.220					
	150 lbs	0.220					
1 ½ "	300 lbs	1.340					
	600 lbs	1.850					

Suitable stem lengths of mechanical thermometers

Dial thermometers

Design of connection	Stem length I ₁					
S/4/5	I ₁ = L - 10 mm	or	$I_1 = U_1 + T - 10 \text{ mm}$			
2	$I_1 = L - 30 \text{mm}$	or	$I_1 = U_1 + T - 30 \text{mm}$			

Ordering information

State: Model / Material / Flange / Instrument connection / Bore size / Thermowell outer diameter / Insertion length U₁ / Optional extras required

Specifications and dimensions given in this leaflet are correct at the time of printing. Modifications may take place and materials specified may be replaced by others without prior notice.

