3.1

Operating Instructions Temperature Transmitter Model T31



T31.10.1P2	



Contents

- Models
- Safety warnings
- Mounting
- **Electrical connections**
- Maintenance
- Notes for mounting and operating in hazardous area
- Safety-engineering values
- Declaration of conformity

Specifications according to WIKA data sheet TE 31.01. Technical alteration rights observed. Issue: May 2006

2294851.03 05/2006 D+GB T31

Alexander Wiegand GmbH & Co. KG

Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Phone (+49) 93 72/132-0 Fax (+49) 93 72/132-406 E-Mail info@wika.de www.wika.de

Models Safety warnings

Models

Head mounting		Ex protection
T31.10.	1P0	without
~~ <u>></u>	1P2	II 1G EEx ia
	1P4	II 2G EEx ib
\checkmark	1P9	II 3G EEx nL/ nA

Safety warnings

When mounting, initiating and operating these transmitters it is important to observe the safety precautions and regulations (e.g. IEC 60 364-6-61).

Nonobservance of the applicable regulations may cause severe injury to persons or damage to equipment.

Only staff with suitable qualification should work with these transmitters.

We draw your attention to the following which must be observed with transmitters with Ex protection:

- · Observe the applicable regulations for the use of Ex-class instruments (e.g.: EN 50 014, EN 50 020, EN 50 021, EN 50 284)
- Observe the notes for mounting and operating in hazardous area described in section 6.
- It is forbidden to use a transmitter that is damaged externally.
- Repairs are forbidden.

Note

Before initial operation check the suitability for the intended application. In particular, it is important to fulfill the ambient and operation conditions as specified in the WIKA data sheet TE 31.01.


3 Mounting

Mounting 3.0 General

These transmitters are designed to be mounted on a measuring insert in a DIN connecting head with form B.

The connecting wires of the measuring insert must be approx. 40 mm long and in-

Mounting example:



3.1 Mounting on measuring insert

3.2 Mounting in connection head

Mounting on measuring insert


The transmitter can be mounted on the circular plate of the measuring insert using two countersunk head M3 screws per **DIN EN 2009.**

Appropriate threaded inserts have been press-fitted in the underside of the case.

Assuming the countersinking is carried out correctly, the permissible screw length can be calculated as follows:

$$I_{max} = s + 4 \text{ mm}$$

Dimensions in mm:



Check the screw length before affixing the transmitter to the measuring insert:

stick the screw in the circular plate and verify additional length of 4 mm!

WARNING

Do not exceed the maximum allowable screw length!

The transmitter will be demaged if the screws are screwed further than 4 mm into the bottom of the transmitter.

Electrical connections

4

!!! Important!!!

Electrical connections

In the case of the transmitters described here there is an internal galvanic connection between the sensor input and analoque output.

No external conducting is to be made (for example, by earthing) between the connected temperature sensor and analogue output!


General

The transmitters have connecting terminals for electrical connection.

We recommend the use of crimped connector sleeves in the case of flexible leads.

4.1 Input Pt100 2 wire

Set a jumper between the input terminals 2 and 3. Otherwise the transmitter signals a sensor burnout and sets the output signal ≥ 22.5 mA.



4.3

Connect 4...20 mA-loop


Maintenance

The electrical connection is made through the terminals (+) and (-).

Connect 4...20 mA-loop

Load diagramm

The permissible load R_A dependent upon the loop power supply voltage $U_{\rm B}$.



maximum permissible terminal voltage:

30 V

 maximum permissible load R_A (dependent upon the loop power supply voltage $U_{\rm B}$)

at **30 V** power supply $U_{\rm B}$


625 Ω at **24V** power supply $U_{\rm B}$

 $R_{s} \leq (U_{s} - 11.5 \text{ V}) / 0.02 \text{ A}$


 R_{a} in Ω and U_{a} in V

3.2 Mounting in connecton head

Insert the measuring insert with the mounted transmitter in the protective sheath and affix in the connecting head using screws in pressure springs.



4.2 Input Pt100 3 wire



5 Maintenance

The temperature transmitters described here are totally maintenance-free!

The electronics are completely encapsulated and incorporate no components which could be repaired or replaced.

Déclaration de

Conformité CE

Document No.

11134755.01

Nous déclarons que les appareils

Transducteur de température, Série

chimie, pour montage dan lé lés de

selon fiche technique valide:

sont conformes aux exidences

essentielles de les directives et

EN 61326:1997 +A1:98 +A2:01

EN 50014:1997 +A1:98 +A2:99

Attestation d'examen CE de type
 DMT 02 ATEX E 106 X de EXAM BBG
 Prüf- und Zertifizier GmbH, Bochum

1) 89/336/CEE (CEM)

2) 94/9/CE (ATEX) (1)

T31.10.1Px

EN 50020:1994

EN 50284:1999

(reg. no. 0158).

3) 94/9/CE (ATEX)

T31.10.009

EN 50021:1999

Types:

T31.10.xxx

Description:

TE 31.01

Notes for mounting and operating in hazardous area

Safety-engineering values

Declaration of conformity

8

Notes for mounting and operating in hazardous area

6.0 General


Use only such a transmitter in a hazardous area that have the corresponding approval for this hazardous area.

The transmitter Model T31.10.1P2 correspond to ignition protection type intrinsically safe apparatus II 1G EEx ia IIC T4/T5/T6.

The transmitter Model T31.10.1P4 correspond to ignition protection type intrinsically safe apparatus II 2G EEx ib IIC T4/T5/T6.

The transmitter Model T31.10.1P9 correspond to ignition protection type energy-limited apparatus II 3G EEx nL IIC T4/T5/T6 and to ignition protection type non-sparking apparatus II 3G EEx nA IIC T4/T5/T6.

Model, Ex protection class, Approval No. and Symbol are stated on the rating plate. Example:



Special conditions for safe use

6.1.1 Mounting in the hazardous area

T31.**.**2/T31.**.**4: Transmitters in a hazardous area are supplied only with associated intrinsically safe apparatus that are approved for this hazardous area. These transmitters must be mounted in a case that must at least correspond to following ingress protection IP 20 according to EN 60 529 / IEC 529.

T31.**.**9 (Use as energy-limited equipment II 3G EEx nL): The supply current circuit must fulfil the requirements for ignition protection type II 3G EEx nL energylimited (EN 50 021). These transmitters must be mounted in a case that must at least correspond to following ingress protection IP 54 according to EN 60 529 / IEC 529.

T31.**.**9 (Use as non-incentive equipment II 3G EEx nA): Disconnection of power supply is forbidden inside the hazardous area. When connecting or disconnecting the terminals ensure the power supply is disconnected outside the hazardous area. These trans-

mitters must be mounted in a case that must at least correspond to following ingress protection IP 54 according to EN 60 529 / IEC 529.

When during use in circuits with the safety class nA (non-incendive) the permissible connected loads have been exceeded for a short term¹⁾, the use of these transmitters in circuits with the safety class EEx nL (energy limited) is not permissible any more.

1) When the transmitters are used in circuits with the safety class nA, it is permissible to exceed the maximum supply voltage by up to 40 % for a short term.

6.1.2 Operating transmitter in Zone 0

The temperature transmitter may be operated only in areas that require apparatus of category 1 when following atmospheric conditions exist:

> temperature: -20 °C ... +60 °C pressure: 0.8 bar ... 1.1 bar

6.1.3 Operating the transmitter in Zone 1 and Zone 2

The transmitter may be used only in the following ambient temperature range according to the temperature class:

T31.10.1P2 II 1G EEx ia

T31.	10.1P 4	II 2G EI	Ex ib
T4:	-50 °C	≤ <i>T</i> _a ≤	+85 °C
T5:	-50 °C	$\leq T_a \leq$	+75 °C
T6:	-50 °C	≤ <i>T</i> _a ≤	+60 °C

101.10.11		11 00 LI	
T4:	-40 °C	≤ <i>T</i> _a ≤	+85 °C
T5:	-40 °C	$\leq T_{\rm a} \leq$	+70 °C
T6:	-40 °C	\leq $T_{\rm a} \leq$	+50 °C

T31 10 1P 0 II 3G FEv nl /nA

Safety-engineering values

7.1 Power Supply / 4 ... 20 mA-

The following safe technical maximum values must not be exceeded:

T31.10.1P 2 II 1G EEx ia	
T31.10.1P4 II 2G EEx ib	
Voltage $U_i = DC 30 V$	
Current $I_i = 100 \text{ mA}$	
Power $P_i = 800 \text{ mW}$	

T31.10.1P 9	II 3G EEx nL/nA
Voltage	$U_{\rm i} = DC 30 V$

Following have an outward effect at the connection terminals (+) und (-) of the transmitter Model T31.10.1P2 and T31.10.1P4: effective internal capacity $C_i = 6.2 \text{ nF}$ effective internal inductivity $L_i = 110 \, \mu$ H Model T31.10.1P9:

effective internal capacity $C_i = 1.2 \text{ nF}$

effective internal inductivity $L_i = 100 \mu H$

7.2 Sensor (terminal 1 to 3)

Connect the sensor according to section 4 to the terminals ①, ② and ③.

The connected sensor must not warm up inadmissably according to the temperature class of the respective hazardous area for the following values for voltage, current and power:

maximum possible values

$$U_{\rm O} = {\rm DC} \, 6.4 \, {\rm V}$$

 $I_{\rm O} = 100 \, {\rm mA}$
 $P_{\rm O} = 426 \, {\rm mW}$

T31.10.1P9 II 3G EEx nL/nA

effective values during operation

$$U_{\rm O} = {\rm DC} \ 2.5 \, {\rm V}$$

 $I_{\rm O} = 1.2 \, {\rm mA}$

The sum of the values of the connected sensor and the connection line must not exceed the following values for the maximum permissible capacity and inductivity:

T31.10.1P2 II 1G EEx ia IIB

T31.10.1P4 II 2G EEx ib IIB

$$C_{\text{sensor}} + C_{\text{line}} < C_{\text{O}}$$
 $C_{\text{O}} = 500 \, \mu\text{F}$
 $C_{\text{sensor}} + L_{\text{line}} < L_{\text{O}}$ $L_{\text{O}} = 10 \, \text{mH}$

(to be continued, see next column)

T31.10.1P 2	II 1G EEx ia IIC
T31.10.1P 4	II 2G EEx ib IIC
$C_{\rm sensor} + C_{\rm line} <$	$C_{\rm O}$ $C_{\rm O}$ = 10 μF
L _{sensor} + L _{line} <	$L_{\rm O}$ $L_{\rm O}$ = 3 mH

T31.10.1P 9	II 3G EEx nL/nA IIC
C _{sensor} + C _{line} <	$C_{\rm O}$ $C_{\rm O}$ = 1000 $\mu {\rm F}$
L _{sensor} + L _{line} <	$L_{\rm O}$ $L_{\rm O}$ = 1000 mH

EG-Konformitäts-EC Declaration of erklärung Conformity

Models

T31.10.xxx

TE 31.01

Description:

Dokument Nr. 11134755.01

Wir erklären, dass d (€iit (€

gekennze (eneten Produkte

Typen:

Beschreibung:

Analoger Temperatur-Transmitter. Chemieausführung, Konfmontage

TE 31.01

die grundlegenden Anforderungen der folgenden Richtlinien und

EN 50014:1997 +A1:98 +A2:99 EN 50020:1994 EN 50020:1994 EN 50284:1999

Document No. 11134755.01

Analogue temperature transmitter

according to the valid data-sheet:

are in conformity with the essential

requirements of the directives and

EN 61326:1997 +A1:98 +A2:01

EN 50014:1997 +A1:98 +A2:99

(1) EC-type-examination certificate DMT 02 ATEX E 106 X of EXAM BBG Prüf- und Zertifizier GmbH, Bochum

1) 89/336/EEC (EMC)

2) 94/9/EC (ATEX) (1)

T31.10.1Px

EN 50020:1994

EN 50020:1994 EN 50284:1999

(reg. no. 0158)

3) 94/9/EC (ATEX)

T31.10.009

EN 50021:1999

Process Industries Series. head

We declare that the marked products

T31.10.xxx

gemäß gültigem Datenblatt:

1) 89/336/EWG (EMV)

EN 61326:1997 +A1:98 +A2:01

2) 94/9/EG (ATEX) (1)

T31.10.1Px

(1) EG-Baumusterprüfbescheinigung DMT 02 ATEX E 106 X von EXAM BBG Prüf- und Zertifizier GmbH,

Bochum (Reg.-Nr. 0158). 3) 94/9/FG (ATEX)

T31 10 009

EN 50021:1999

WIKA Alexander Wiegand GmbH & Co. KG

Klingenberg, 2006-05-08 Geschäftsbereich TRONIC

Company division TRONIC

Qualitätsmanagement Quality management Management de la qualité

TRONIC TRONIC

i A Thomas Gerling