


Flow Measurement Capabilities



Part of your business

About Us

As a family-run business acting globally, with over 10,000 highly qualified employees, the WIKA group of companies is a worldwide leader in pressure and temperature measurement. The company also sets the standard in the measurement of level, flow, force, and in calibration technology.

With numerous wholly owned subsidiaries and partners, WIKA competently and reliably supports its customers worldwide. Our experienced engineers and sales experts are your competent and dependable contacts locally.



Alexander Wiegand,
Chairman and CEO, WIKA

Able to Meet Any Challenge

WIKA Flow offers a broad portfolio of flow measuring instruments and support services, from the planning phase through process integration. We provide tailored flow measurement solutions for our customers worldwide

- Extensive primary flow component product range
- Global production and engineering network
- Subsidiary calculation center and flow calibration laboratory certified in accordance with ISO 17025

In addition to technical implementation and engineering, WIKA Flow also pays attention to our customers' operating costs and budgets, contributing to value creation.

- High accuracy
- Ease of maintenance
- Low pressure loss
- Small footprint

Manufacturing locations



Euromisure, Italy



Euromisure, Italy



Micro Precision, India



WIKI Flow, USA

Contents

Flow Measuring Instruments at a Glance	4
Energy Efficiency and Savings	6
Engineered Solutions	10
Accessories	12
Long-term Reliability	13
You Have Specific Requirements. We Have the Experts.	14
WIKA Worldwide	16

Competent and Reliable

High accuracy is a decisive criterion in many applications for flow measurement, especially in high-tech fields. It creates the conditions for the functionality and cost-effectiveness of each process.

In order to fulfill accuracy requirements consistently, measuring instruments must be calibrated regularly. Our calibration laboratory can check all types of flow meters, both primary (Venturi tubes, orifice plates) and secondary (MAG and ultrasonic flow meters). The calibration is carried out in accordance with ISO/EC 17025 on the basis of gravimetric method (reference standard: ISO-4185:1980).



Calibration testing line

	RIG 1	RIG 2	RIG 3	RIG 4
Max. overall weight	32,000 kg	7,000 kg	1,500 kg	400 kg
Flow range	300 ... 2,700 m ³ /h	50 ... 700 m ³ /h	10 ... 125 m ³ /h	0.8 ... 25 m ³ /h
Line size	12 ... 20"	6 ... 10"	4 ... 6"	< 6"

Flow Measuring Instruments at a Glance

The most common method for measuring flow is based on the differential pressure principle. This principle is proven and applicable for all common types of media. Therefore WIKA Flow primary flow elements use the differential pressure principle to effectively measure flow.

We can combine flow elements with differential pressure measuring instruments or accessories to create economical complete solutions. Additionally, WIKA Flow is able to assemble other measurement technology to meet our customers' needs.

Primary flow elements

		
Orifice plates and flanges	Nozzles	Cone flow meters
		
Restriction orifices	Venturi tubes	Wedge flow meters
		
Meter runs	Pitot tubes	Engineered solutions

With our extensive product range, from standard to customer-specific solutions, we are able to meet all challenges in the flow measurement. WIKA Flow measurement instruments and accessories comply with all major international directives, feature worldwide approvals, and meet the highest standards of quality and safety.

Additional products



Air flow sensors



Flow switches

Accessories



Utility feed headers



Condensate and seal pots

Compact and Smart

We make it easier for our customers to implement their measuring points by supplying ready-made measuring arrangements, consisting of the respective flow element and high-quality measurement technology (differential pressure transmitters, electrical thermometer for temperature compensation). The compact assemblies can be effortlessly integrated into the process.

Orifice plates

Simple to install and easy to maintain: Orifice plates are the most commonly used flow element. Depending on the application, there are also versions with measuring flanges and annular chambers.



With smart solutions like this, not only do our customers reduce both their acquisition and installation costs, but they also lower their maintenance costs, since the number of leakages can be reduced by up to 70 percent with professionally installed and tested measuring systems.


FloTec pitot tube

The pitot tube measures media in closed lines using multiple sensing. Due to its small footprint, permanent pressure loss is significantly reduced. (Fixed version pictured here.)



HHR ProPak


The ProPak flow meter has defined new performance standards for applications in the oil and gas industries. The instrument is approved for measurements requiring verification in accordance with API 22.2.



Energy Efficient

Differential pressure flow meters generally cause a permanent pressure drop in the process. This must be compensated by additional pumping capacity. The required energy demand for this can increase the annual operating costs, sometimes significantly.

HHR flow tubes, Venturi tubes, and pitot tubes demonstrate that they can reduce the pressure drop and thus operate energy efficiently. They have been designed for a wide range of applications.



Venturi tubes and HHR flow tubes provide the highest level of traceable accuracy with minimal pressure loss. The main advantage of the FloTec pitot tubes lies in an even lower pressure drop (<10 % of the differential pressure) as well as in the constant measurement accuracy over a wide range of Reynolds numbers.




Space Saving

A flow measurement with primary elements requires, as a rule, a straight upstream and downstream pipe. This can be comparatively long, depending on the flow conditions and accuracy requirements, and calls for the corresponding space requirement. WIKA has therefore developed flow meters specifically for applications with limited mounting space which also offer a high accuracy without long meter runs.


HHR FlowPak

The HHR FlowPak flow meter is a technological advancement in flow profile formation.

It does not require any upstream and downstream pipes and can even be fitted following two 90° pipe elbows.



The HHR FlowPak is thus the optimal solution for applications with limited space. At the same time, the instrument meets the requirements for high accuracy, low operating costs, and a long service life.



FloCone cone flow meter

The cone flow meter is also ideal for compact installation situations. Due to an optimized flow profile, only a very short upstream and downstream pipe is required. Nevertheless, the robust instrument offers a wide and stable turndown and, at the same time, a high accuracy and repeatability.



The FLC-FC cone flow meter is produced in accordance with the ISO 5167 reference standard. Part 5 of this standard refers to the installation and operating conditions and gives further information for calculating the flow rate and its uncertainties.

Critical Media

For every flow measurement, critical media represent a special challenge. Whether aggressive liquids, highly viscous liquids, or erosive slurries: We have a solution for each application with corresponding measurement characteristics and durability.

Special orifice plates

Quarter circle and conical entrance orifice plates, segmental orifice plates and eccentric orifice plates are, in many cases, the best choice for measuring liquids with low Reynolds numbers and liquids with higher densities. These instruments, which are as simple as they are effective, are proven over a long time. These orifice plates are also available in versions with orifice flanges and annular chambers.



Wedge flow meter

Due to its construction with a V-shaped wedge, the wedge flow meter is well suited for measuring the flow of slurry and highly viscous media. It is also extremely robust against particle-laden, abrasive, and erosive media.


In the case of aggressive media, the differential pressure measuring instrument installed on the wedge element is subject to influences that can lead to measuring errors and damage the instrument. For continuous and problem-free measured value registration, WIKA therefore offers a complete solution with a diaphragm seal system. In this way, the process transmitter is securely separated from the process.



Meter Runs

For the highest possible accuracy, primary flow elements are generally integrated into the process as meter runs, thus as a unit with upstream and downstream pipes. Meter runs are also available in a threaded design with a flow measurement add-on. If a higher accuracy is required, the instrument must be calibrated.

With the implementation of meter runs, WIKA relieves its customers of all effort: Even before the order is placed, our qualified on-site service team records all required dimensions and parameters. We design, build, and test the meter run to the desired specification. Subsequently, we will then install it professionally and ready-for-operation into the plant.



Designed in accordance with the following standards: ISO5167-1:2003, ASME MFC-3M or AGA3

Flow nozzle test sections

These precise measuring instruments are manufactured exactly in accordance with the provisions of the ASME PTC6 standard for steam turbines. They are used in the acceptance testing of power plant turbines.

The nozzles measure the flow of boiler feed water and condensate. WIKA has already delivered more than 300 assemblies of this type to energy companies.



Restriction Orifices

To correctly perform the measurement task, in some processes, the flow rate must be limited or the pressure reduced. For this purpose, a restriction orifice is installed in the pipeline, either in a single-step design or – particularly in the case of high differential pressures – as a multi-step restrictor.

Each restriction orifice is an application-specific solution. It is designed by our experienced specialists, depending on media properties, pressure loss, and process data. Performance and dimensions are calculated to exclude the potential negative effects of sound, noise levels, and cavitation.

Safety is a top priority at WIKA. Since, in the chemical and pharmaceutical industries, different substances and active ingredients are often produced in the same plant, there must be no risk of leakage from the measuring instruments used in the process. For such processes, there is the multi-step restriction orifice as a special design without dissimilar material welds, which prevents potential media leakage.



Accessories


Our comprehensive accessory program includes a wide variety of equipment to complement the individual instruments. A complete solution is not only quickly and easily configured, but can also be installed in the same manner.




Flow straighteners: Tube bundles, perforated plates, and internal tab types




Utility feed headers



Valve manifolds for shutting off, pressure compensating as well as purging and venting differential pressure measuring instruments



Flap indicators for the flow measurement of transparent liquids, sight glass version (for flow only) also available



Condensate and seal pots are used as a barrier between the main line and the secondary instruments in the flow and pressure measurement of liquids, steam, or other vapours that can affect secondary instruments.

Long-Term Reliability


The technical reliability of our products for an accurate and repeatable flow measurement is critical to safe and efficient plant operation. Our solutions have been designed for long life without performance restrictions, even under harsh operating conditions.

This is ensured by simple configuration, process integration, and maintenance as well as carefully selected materials and components.

Our delivery reliability doesn't allow for the creation of any bottlenecks. All flow measurement products are available in the long term and are delivered to customers on time.

High velocity

Flow nozzles provide reliable, accurate flow measurement and long-term repeatability, particularly in steam applications with high flow velocities.



Even distribution

Radiant Venturi nozzles are used, for example, in steam cracking furnaces and are installed there at the inlet of each radiant coil. The nozzles provide even flow distribution, even when the pressure loss increases due to uneven coking in one or more coils.

Control of the media mix

In the blower systems of combustion furnaces, the adjustment of the fuel-air ratio to the firing capacity is controlled by Venturi tubes.

In such cases, the flow meters are referred to as aspirators or proportional mixers.



We Have the Experts for Your Requirements

Many measuring tasks can be fulfilled with standard products. However, for a large number of requirements, an individual approach is essential. With our comprehensive technological know-how and a unique level of in-house production depth, we can provide you with the optimum solution for your application.

When developing a measurement solution, our experts around the world rely on internet-based dimensioning software that is protected by copyright. It enables a design calculation in accordance with the ISO 5167: 2003, ASME MFC-3M and AGA3 standards. In addition, there is an interface for the calculation of flow elements and restriction orifices, in the latter with special consideration of the problems of throttling, sound, noise and cavitation. In addition, the software includes a multi-stage calculation option for liquid and gas.

The parameters required for dimensioning the measurement solution can be transmitted by the customer via the input mask.



Trust through quality

We offer our customers outstanding quality, which is maintained through permanent checks. We place the same high demands on our suppliers. For only with excellent initial and intermediate products can we deliver consistently reliable products to you.

Extensive Test Procedures

Liquid penetrant inspection (LPI) is used to locate surface defects on relatively smooth and non-porous materials. This test method is normally used for welded parts to guarantee a good quality of the weld surface.

Magnetic particle inspection (MPI) is a non-destructive test method for the detection of surface and sub-surface discontinuities in ferrous materials.

X-ray testing based on the differing absorption of penetrating radiation. Thus it can detect differences in density due to material composition, thickenings, flaws and welded or soldered joints. X-ray tests are normally used for components that must fulfil critical requirements.

Hydrostatic pressure tests (HT) are used to (statically) test assemblies, piping systems and Venturi tubes under their working pressure. The hydrostatic pressure and strength test is conducted with water at ambient temperatures.

Ultrasonic testing is a method in which high-frequency sound waves are introduced into a material. Any surface or subsurface discontinuities or flaws that are present interrupt the sound waves and reflect a proportion of them. Ultrasonic testing often replaces X-ray methods.

Positive material identification commonly applies spectroscopy with X-ray fluorescence analysis. This testing of material composition is ideally suited for proving the accuracy of material certificates or for identifying material.

All Around the World – Close to Our Customers

Capability and flexibility

Proximity to our customers is essential for efficient solutions. Whether standard products or custom designs: Working with you we'll find the right concepts for your requirements.

As a provider of high added-value solutions to our customers, WIKA offers a quick dimensioning service combined with localized fast delivery shops.

Whether it be scheduled maintenance or unplanned urgent replacement, WIKA can always meet your needs.



WIKA Worldwide

Europe

Austria
WIKA Messgerätevertrieb
Ursula Wiegand GmbH & Co. KG
Perfektastr. 73
1230 Vienna
Tel. +43 1 8691631
Fax: +43 1 8691634
info@wika.at
www.wika.at

Belarus
WIKA Belrus
Ul. Zaharova 50B, Office 3H
220088 Minsk
Tel. +375 17 2244164
Fax: +375 17 2635711
info@wika.by
www.wika.by

Benelux
WIKA Benelux
Industrial estate De Berk
Newtonweg 12
6101 WX Echt
Tel. +31 475 535500
info@wika.nl
www.wika.nl

Bulgaria
WIKA Bulgaria EOOD
Akad. Ivan Geshov Blvd. 2E
Business Center Serdika, building 3
Office 3/104
1330 Sofia
Tel. +359 2 82138-10
Fax: +359 2 82138-13
info@wika.bg
www.wika.bg

Croatia
WIKA Croatia d.o.o.
Hrastovicka 19
10250 Zagreb-Lucko
Tel. +385 1 6531-034
Fax: +385 1 6531-357
info@wika.hr
www.wika.hr

Denmark
WIKA Danmark A/S
Banevænget 13
3460 Birkerød
Tel. +45 4581 9600
info@wika.as
www.wika.as

Finland
WIKA Finland Oy
Melkonkatu 24
00210 Helsinki
Tel. +358 9 682492-0
Fax: +358 9 682492-70
info@wika.fi
www.wika.fi

France
WIKA Instruments s.a.r.l.
Immeuble Le Trident
38 avenue du Gros Chêne
95220 Herblay
Tel. +33 1 787049-46
Fax: +33 1 787049-59
info@wika.fr
www.wika.fr

Germany
WIKA Alexander Wiegand SE & Co. KG
Alexander-Wiegand-Str. 30
63911 Klingenberg
Tel. +49 9372 132-0
Fax: +49 9372 132-406
info@wika.de
www.wika.de

Italy
WIKA Italia S.r.l. & C. S.a.s.
Via G. Marconi 8
20020 Arese (Milano)
Tel. +39 02 93861-1
Fax: +39 02 93861-74
info@wika.it
www.wika.it

Poland
WIKA Polska spółka z ograniczoną
odpowiedzialnością sp. k.
Ul. Legska 29/35
87-800 Wloclawek
Tel. +48 54 230110-0
Fax: +48 54 230110-1
info@wikapolska.pl
www.wikapolska.pl

Romania
WIKA Instruments Romania S.R.L.
050897 Bucuresti
Calea Rahovei Nr. 266-268
Corp 61, Etaj 1
Tel. +40 21 4048327
Fax: +40 21 4563137
info@wika.ro
www.wika.ro

Russia
AO "WIKI MERA"
Sosenskoye settlement
Nikolo-Khovanskoye, 1011A / 1
office 2 / 2.09
142770, Moscow
Tel. +7 495-648018-0
info@wika.ru
www.wika.ru

Serbia
WIKA Merna Tehnika d.o.o.
Sime Solajac 15
11060 Beograd
Tel. +381 11 2763722
Fax: +381 11 2753674
info@wika.rs
www.wika.rs

Spain
Instrumentos WIKI S.A.U.
C/ Josep Carner, 11-17
08205 Sabadell Barcelona
Tel. +34 933 9386-30
Fax: +34 933 9386-66
info@wika.es
www.wika.es

Switzerland
WIKA Schweiz AG
Industriestrasse 11
6285 Hitzkirch
Tel. +41 41 91972-72
Fax: +41 41 91972-73
info@wika.ch
www.wika.ch

Turkey
WIKA Instruments
Endüstriyel Ölçüm Cihazları Tic. Ltd. Şti.
Şerifali Mah. Bayraktar Bulvarı No:17
34775 Ümraniye, İstanbul
Tel. +90 216 41590-66
Fax: +90 216 41590-97
info@wika.com.tr
www.wika.com.tr

Ukraine
TOV WIKI Prylad
Str. Generala Almazova, 18/7
Office 101
01133 Kiev
Tel. +38 044 496 83 80
Fax: +38 044 496 83 80
info@wika.ua
www.wika.ua

United Kingdom
WIKA Instruments Ltd
Merstham, Redhill RH13LG
Tel. +44 1737 644-008
Fax: +44 1737 644-403
info@wika.co.uk
www.wika.co.uk

North America

Canada
WIKA Instruments Ltd.
Head Office
3103 Parsons Road
Edmonton, Alberta, T6N 1C8
Tel. +1 780 463-7035
Fax: +1 780 462-0017
info@wika.ca
www.wika.ca

USA
WIKA Instrument, LP
1000 Wiegand Boulevard
Lawrenceville, GA 30043
Tel. +1 770 513-8200
Fax: +1 770 338-5118
info@wika.com
www.wika.com

Gayesco-WIKA USA, LP
229 Beltway Green Boulevard
Pasadena, TX 77503
Tel. +1 713 475-0022
Fax: +1 713 475-0011
office 2 / 2.09
info@wikahouston.com
www.wika.us

Mensor Corporation
201 Barnes Drive
San Marcos, TX 78666
Tel. +1 512 396-4200
Fax: +1 512 396-1820
sales@mensor.com
www.mensor.com

WIKA Instrument, LP
1213 Antler Drive
Weslaco, TX 78693
Tel. +1 817 473-4481
Fax: +1 817 473-6310
info@wika.com
www.wika.com

Latin America

Argentina
WIKA Argentina S.A.
Gral. Lavalle 3568
(B1603AUH) Villa Martelli
Buenos Aires
Tel. +54 11 47301800
Fax: +54 11 47610050
info@wika.com.ar
www.wika.com.ar

Brazil
WIKA do Brasil Ind. e Com. Ltda.
Av. Úrsula Wiegand, 03
18560-000 Iperó - SP
Tel. +55 15 3459-9700
Fax: +55 15 3266-1196
vendas@wika.com.br
www.wika.com.br

Chile
WIKA Chile S.p.A.
Los Leones 2209
Providencia Santiago
Tel. +56 2 2209-2195
info@wika.cl
www.wika.cl

Colombia
Instrumentos WIKI Colombia S.A.S.
Avenida Carrera 63 # 98 - 25
Bogotá - Colombia
Tel. +57 1 624 0564
info@wika.co
www.wika.co

Mexico
Instrumentos WIKI Mexico
S.A. de C.V.
Calzada San Isidro No. 97 P1-1
Col. San Francisco Tetecala Deleg.
Azcapotzalco
Ciudad de Mexico CP 02730
Tel. +52 55 50205300
Fax: +52 55 50205300
ventas@wika.com
www.wika.mx

Asia

China
WIKA Instrumentation Suzhou Co., Ltd.
81, Ta Yuan Road, SND
Suzhou 215011
Tel. +86 512 6878 8000
Fax: +86 512 6809 2321
info@wika.cn
www.wika.com.cn

India
WIKA Instruments India Pvt. Ltd.
Village Kesnand, Wagholi
Pune - 412 207
Tel. +91 20 66293-200
Fax: +91 20 66293-325
sales@wika.co.in
www.wika.co.in

Japan
WIKA Japan K. K.
MG Shibaura Bldg. 6F
1-8-4, Shibaura, Minato-ku
Tokyo 105-0023
Tel. +81 3 5439-6673
Fax: +81 3 5439-6674
info@wika.co.jp
www.wika.co.jp

Kazakhstan
TOO WIKI Kazakhstan
Microdistrict 1, 50/2
050036 Almaty
Tel. +7 727 225 9444
Fax: +7 727 225 9777
info@wika.kz
www.wika.kz

Korea
WIKA Korea Ltd.
39 Gajangsaneopseo-ro Osan-si
Gyeonggi-do 447-210
Tel. +82 2 869-0505
Fax: +82 2 869-0525
info@wika.co.kr
www.wika.co.kr

Malaysia
WIKA Instrumentation (M) Sdn. Bhd.
No. 23, Jalan Jurukur U1/19
Hicom Glenmarie Industrial Park
40150 Shah Alam, Selangor
Tel. +60 3 5590 6666
info@wika.my
www.wika.my

Philippines
WIKA Instruments Philippines Inc.
Ground Floor, Suite A
Rose Industries Building
#11 Pioneer St., Pasig City
Philippines 1600
Tel. +63 2 234-1270
Fax: +63 2 654-9662
info@wika.ph
www.wika.ph

Singapore
WIKA Instrumentation Pte. Ltd.
13 Kian Teck Crescent
628878 Singapore
Tel. +65 6844 5506
Fax: +65 6844 5507
info@wika.sg
www.wika.sg

Taiwan
WIKA Instrumentation Taiwan Ltd.
Min-Tsu Road, Pinjen
32451 Taoyuan
Tel. +886 3 420 6052
Fax: +886 3 490 0080
info@wika.tw
www.wika.tw

Thailand
WIKA Instrumentation Corporation
(Thailand) Co., Ltd.
850/7 Ladkrabang Road, Ladkrabang
Bangkok 10520
Tel. +66 2 32668-73
Fax: +66 2 32668-74
info@wika.co.th
www.wika.co.th

Africa / Middle East

Egypt
WIKI Near East Ltd.
Villa No. 6, Mohamed Fahmy
Elmohdar St. - of Eltayaran St.
1st District - Nasr City - Cairo
Tel. +20 2 240 13130
Fax: +20 2 240 13113
info@wika.com.eg
www.wika.com.eg

Namibia
WIKI Instruments Namibia Pty Ltd.
P.O. Box 31263
Pionierspark
Windhoek
Tel. +26 4 61238811
Fax: +26 4 6123403
info@wika.com.na
www.wika.com.na

Saudi Arabia
WIKI Saudi Arabia Llc
Wh#3, Al Tawuun Al Khobar 34644
Baghlah Al Sanaiya Aziziya
Plan Sh-Kh 564, Land No 13&15
Al Khobar
Tel. +966 53 555 0874
mohammed.khaiz@wika.com
www.wika.ae

South Africa
WIKI Instruments Pty. Ltd.
Chilvers Street, Denver
Johannesburg, 2094
Tel. +27 11 62100-00
Fax: +27 11 62100-59
sales@wika.co.za
www.wika.co.za

United Arab Emirates
WIKI Middle East FZE
Warehouse No. RB08JB02
P.O. Box 17492
Jebel Ali, Dubai
Tel. +971 4 883-9090
Fax: +971 4 883-9198
info@wika.ae
www.wika.ae

Australia

Australia
WIKI Australia Pty. Ltd.
Unit K, 10-16 South Street
Rydalmere, NSW 2116
Tel. +61 2 88455222
Fax: +61 2 96844767
sales@wika.com.au
www.wika.com.au

New Zealand
WIKI Instruments Limited
Unit 7 / 49 Sainsbury Road
St Lukes - Auckland 1025
Tel. +64 9 8479020
Fax: +64 9 8465964
info@wika.co.nz
www.wika.co.nz

WIKA USA

1000 Wiegand Boulevard
Lawrenceville, GA 30043
Toll Free 1-888-WIKA-USA (945-2872)
Tel (770) 513-8200 Fax (770) 338-5118
info@wika.com • www.wika.com

B053 - 1000 01/20

WIKI® is a registered trademark of WIKI Alexander Wiegand SE & Co. KG., used under license by WIKI Instrument, LP
Copyright 2019 WIKI Instrument, LP. All Rights Reserved.



Part of your business